Dora product family

DORA

Ensto Dora is an energy-efficient panel luminaire series utilizing modern backlit technology. Dora is an ideal solution for offices, meeting rooms, public spaces, stairwells, and dining areas. Thanks to its IP55 rating, it is also perfectly suited for healthcare facilities and hospitals.



DALI

DALI drivers enable luminaires to be connected to DALI based control systems and Smart Buildings. Compared to a fixed output installation, the dimming and individual control capability provided by DALI enables considerable energy savings and control, depending on luminaire specifications.

Tunable White

Ensto luminaires with Tunable White solution are a base for Human Centric lighting. You can integrate Ensto Tunable White luminaires into numerous control systems which operate steplessly between 2700 K and 6500 K. Tunable White solution is perfect for modern office use.





Structure

- Frame made of aluminum and body of white painted steel
- Opal (O) or microprismatic (M) optics
- Luminaire IP55 from below, IP20 from above
- Power/luminous flux selectable from DIP switches on the control gear (see table)
- Microprismatic versions UGR<19
- Selection:
  600X600, 300X1200, 300X600, 600X1200
- LED module lifespan T_a=25 °C:
  >100 000 h (L70)
  >100 000 h (L80)
  71 000 h (L90)
- LED driver life time T_a=25 °C:
  100 000 h (max. 10 % failure)

Mounting

- T-bar ceiling and surface mounting with a separate surface mounting frame or concealed bracket for symmetrical T-bar systems
- Suspension with a separate suspension kit for 600x600 mm and 600x1200 mm, maximum suspension length 1500 mm
- -o- 3x2,5 mm² and 5x2,5 mm² (DALI)
- Driver supply placed on top or next to the panel

Made to order

- Connection cables and solutions according to the project

E number	Type	Product name	Control	Optic	Weight	L x W x H	Power	Luminous flux	lm/W
Dora LED 600x600 - microprismatic optics - 840									
42 022 34	D06X6M/840	D06X6M 4420LM 28,1W/840 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	28,1 W	4 420 lm	157 lm/W
42 022 92	D06X6M21/840	D06X6M 2110LM 13,5W/840 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	13,5 W	2 110 lm	156 lm/W
42 022 93	D06X6M30/840	D06X6M 3020LM 18,9W/840 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	18,9 W	3 020 lm	160 lm/W
42 022 94	D06X6M33/840	D06X6M 3320LM 20,8W/840 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	20,8 W	3 320 lm	160 lm/W
42 022 95	D06X6M41/840	D06X6M 4160LM 26,4W/840 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	26,4 W	4 160 lm	158 lm/W
42 022 96	D06X6M50/840	D06X6M 4980LM 32,0W/840 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	32,0 W	4 980 lm	156 lm/W
42 022 97	D06X6M55/840	D06X6M 5510LM 35,8W/840 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	35,8 W	5 510 lm	154 lm/W
42 022 98	D06X6M58/840	D06X6M 5830LM 38,0W/840 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	38,0 W	5 830 lm	153 lm/W
42 022 30	D06X6MED/840	D06X6M 4420LM 28,1W/840 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	28,1 W	4 420 lm	157 lm/W
42 022 38	D06X6M21ED/840	D06X6M 2110LM 13,5W/840 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	13,5 W	2 110 lm	156 lm/W
42 022 39	D06X6M30ED/840	D06X6M 3020LM 18,9W/840 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	18,9 W	3 020 lm	160 lm/W
42 022 40	D06X6M33ED/840	D06X6M 3320LM 20,8W/840 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	20,8 W	3 320 lm	160 lm/W
42 022 41	D06X6M41ED/840	D06X6M 4160LM 26,4W/840 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	26,4 W	4 160 lm	158 lm/W
42 022 42	D06X6M50ED/840	D06X6M 4980LM 32,0W/840 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	32,0 W	4 980 lm	156 lm/W
42 022 43	D06X6M55ED/840	D06X6M 5510LM 35,8W/840 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	35,8 W	5 510 lm	154 lm/W
42 022 44	D06X6M58ED/840	D06X6M 5830LM 38,0W/840 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	38,0 W	5 830 lm	153 lm/W
42 601 88	D06X6M41T/840	D06X6M 4160LM 26,4W/840 MP TRI	TRIAC	Microprism	2,7 kg	595 x 595 x 33 mm	26,4 W	4 160 lm	158 lm/W
42 601 91	D06X6M61T/840	D06X6M 6122LM 39,9W/840 MP TRI	TRIAC	Microprism	2,7 kg	595 x 595 x 33 mm	39,9 W	6 120 lm	153 lm/W
Dora LED 600x600 - microprismatic optics - 830									
42 022 99	D06X6M/830	D06X6M 4450LM 30,0W/830 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	30,0 W	4 450 lm	148 lm/W
42 289 16	D06X6M20/830	D06X6M 2000LM 13,5W/830 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	13,5 W	2 000 lm	148 lm/W
42 289 17	D06X6M31/830	D06X6M 3140LM 20,8W/830 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	29,8 W	3 140 lm	105 lm/W
42 289 18	D06X6M34/830	D06X6M 3410LM 22,7W/830 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	22,7 W	3 410 lm	150 lm/W
42 289 19	D06X6M42/830	D06X6M 4180LM 28,1W/830 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	28,1 W	4 180 lm	149 lm/W
42 289 20	D06X6M50/830	D06X6M 4970LM 34,0W/830 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	34,0 W	4 970 lm	146 lm/W
42 289 21	D06X6M55/830	D06X6M 5510LM 38,0W/830 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	38,0 W	5 510 lm	145 lm/W
42 022 45	D06X6MED/830	D06X6M 4450LM 30,0W/830 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	30,0 W	4 450 lm	148 lm/W
42 022 46	D06X6M20ED/830	D06X6M 2000LM 13,5W/830 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	13,5 W	2 000 lm	148 lm/W
42 022 47	D06X6M31ED/830	D06X6M 3140LM 20,8W/830 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	20,8 W	3 140 lm	151 lm/W
42 022 48	D06X6M34ED/830	D06X6M 3410LM 22,7W/830 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	22,7 W	3 410 lm	150 lm/W
42 022 49	D06X6M42ED/830	D06X6M 4180LM 28,1W/830 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	28,1 W	4 180 lm	149 lm/W
42 022 50	D06X6M50ED/830	D06X6M 4970LM 34,0W/830 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	34,0 W	4 970 lm	146 lm/W
42 022 51	D06X6M55ED/830	D06X6M 5510LM 38,0W/830 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	38,0 W	5 510 lm	145 lm/W
42 601 86	D06X6M39T/830	D06X6M 3930LM 26,4W/830 MP TRI	TRIAC	Microprism	2,7 kg	595 x 595 x 33 mm	26,4 W	3 930 lm	149 lm/W
42 601 89	D06X6M58T/830	D06X6M 5785LM 39,9W/830 MP TRI	TRIAC	Microprism	2,7 kg	595 x 595 x 33 mm	39,9 W	5 790 lm	145 lm/W

© We reserve the right to changes.

E number	Type	Product name	Control	Optic	Weight	L x W x H	Power	Luminous flux	lm/W
Dora LED 600x600 - microprismatic optics - 940									
42 022 35	D06X6M/940	D06X6M 4390LM 30,0W/940 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	30,0 W	4 390 lm	146 lm/W
42 289 22	D06X6M20/940	D06X6M 1970LM 13,5W/940 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	13,5 W	1 970 lm	146 lm/W
42 289 23	D06X6M30/940	D06X6M 3090LM 20,8W/940 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	20,8 W	3 090 lm	149 lm/W
42 289 24	D06X6M34/940	D06X6M 3360LM 22,7W/940 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	22,7 W	3 360 lm	148 lm/W
42 289 25	D06X6M41/940	D06X6M 4130LM 28,1W/940 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	28,1 W	4 130 lm	147 lm/W
42 289 26	D06X6M49/940	D06X6M 4900LM 34,0W/940 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	34,0 W	4 900 lm	144 lm/W
42 289 27	D06X6M54/940	D06X6M 5430LM 38,0W/940 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	38,0 W	5 430 lm	143 lm/W
42 022 31	D06X6MED/940	D06X6M 4390LM 30,0W/940 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	30,0 W	4 390 lm	146 lm/W
42 022 52	D06X6M20ED/940	D06X6M 1970LM 13,5W/940 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	13,5 W	1 970 lm	146 lm/W
42 022 53	D06X6M30ED/940	D06X6M 3090LM 20,8W/940 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	20,8 W	3 090 lm	149 lm/W
42 022 54	D06X6M34ED/940	D06X6M 3360LM 22,7W/940 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	22,7 W	3 360 lm	148 lm/W
42 022 55	D06X6M41ED/940	D06X6M 4130LM 28,1W/940 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	28,1 W	4 130 lm	147 lm/W
42 022 56	D06X6M49ED/940	D06X6M 4900LM 34,0W/940 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	34,0 W	4 900 lm	144 lm/W
42 022 57	D06X6M54ED/940	D06X6M 5430LM 38,0W/940 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	38,0 W	5 430 lm	143 lm/W
42 601 56	D06X6MED/9TW	D06X6M 4390LM 30,0W/927-65 MP DALI	Tunable White	Microprism	2,7 kg	595 x 595 x 33 mm	30,0 W	4 390 lm	146 lm/W
Dora LED 600x600 - microprismatic optics - 930									
42 289 28	D06X6M/930	D06X6M 4410LM 32,0W/930 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	32,0 W	4 410 lm	138 lm/W
42 289 29	D06X6M19/930	D06X6M 1870LM 13,5W/930 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	13,5 W	1 870 lm	139 lm/W
42 289 30	D06X6M29/930	D06X6M 2930LM 20,8W/930 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	20,8 W	2 930 lm	141 lm/W
42 289 31	D06X6M34/930	D06X6M 3440LM 24,6W/930 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	24,6 W	3 440 lm	140 lm/W
42 289 32	D06X6M42/930	D06X6M 4160LM 30,0W/930 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	30,0 W	4 160 lm	139 lm/W
42 289 33	D06X6M49/930	D06X6M 4880LM 35,8W/930 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	35,8 W	4 880 lm	136 lm/W
42 289 34	D06X6M52/930	D06X6M 5150LM 38,0W/930 MP	ON/OFF	Microprism	2,7 kg	595 x 595 x 33 mm	38,0 W	5 150 lm	136 lm/W
42 022 58	D06X6MED/930	D06X6M 4410LM 32,0W/930 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	32,0 W	4 410 lm	138 lm/W
42 022 59	D06X6M19ED/930	D06X6M 1870LM 13,5W/930 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	13,5 W	1 870 lm	139 lm/W
42 022 60	D06X6M29ED/930	D06X6M 2930LM 20,8W/930 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	20,8 W	2 930 lm	141 lm/W
42 022 61	D06X6M34ED/930	D06X6M 3440LM 24,6W/930 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	24,6 W	3 440 lm	140 lm/W
42 022 62	D06X6M42ED/930	D06X6M 4160LM 30,0W/930 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	30,0 W	4 160 lm	139 lm/W
42 022 63	D06X6M49ED/930	D06X6M 4880LM 35,8W/930 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	35,8 W	4 880 lm	136 lm/W
42 022 64	D06X6M52ED/930	D06X6M 5150LM 38,0W/930 MP DALI	DALI	Microprism	2,7 kg	595 x 595 x 33 mm	38,0 W	5 150 lm	136 lm/W
Dora LED 600x600 - opal diffuser - 840									
42 022 36	D06X60/840	D06X60 4410LM 26,4W/840 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	26,4 W	4 410 lm	167 lm/W
42 289 35	D06X6022/840	D06X60 2240LM 13,5W/840 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	13,5 W	2 240 lm	166 lm/W
42 289 36	D06X6032/840	D06X60 3200LM 18,9W/840 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	18,9 W	3 200 lm	169 lm/W
42 289 37	D06X6035/840	D06X60 3520LM 20,8W/840 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	20,8 W	3 520 lm	169 lm/W
42 289 38	D06X6041/840	D06X60 4120LM 24,6W/840 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	24,6 W	4 120 lm	167 lm/W
42 289 39	D06X6050/840	D06X60 4980LM 30,0W/840 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	30,0 W	4 980 lm	166 lm/W
42 289 40	D06X6056/840	D06X60 5570LM 34,0W/840 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	34,0 W	5 570 lm	164 lm/W
42 289 41	D06X6062/840	D06X60 6180LM 38,0W/840 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	38,0 W	6 180 lm	163 lm/W
42 022 32	D06X60ED/840	D06X60 4410LM 26,4W/840 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	26,4 W	4 410 lm	167 lm/W
42 022 65	D06X6022ED/840	D06X60 2240LM 13,5W/840 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	13,5 W	2 240 lm	166 lm/W
42 022 66	D06X6032ED/840	D06X60 3200LM 18,9W/840 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	18,9 W	3 200 lm	169 lm/W
42 022 67	D06X6035ED/840	D06X60 3520LM 20,8W/840 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	20,8 W	3 520 lm	169 lm/W
42 022 68	D06X6041ED/840	D06X60 4120LM 24,6W/840 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	24,6 W	4 120 lm	167 lm/W
42 022 69	D06X6050ED/840	D06X60 4980LM 30,0W/840 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	30,0 W	4 980 lm	166 lm/W
42 022 70	D06X6056ED/840	D06X60 5570LM 34,0W/840 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	34,0 W	5 570 lm	164 lm/W
42 022 71	D06X6062ED/840	D06X60 6180LM 38,0W/840 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	38,0 W	6 180 lm	163 lm/W

© We reserve the right to changes.

E number	Type	Product name	Control	Optic	Weight	L x W x H	Power	Luminous flux	lm/W
Dora LED 600x600 - opal diffuser - 830									
42 289 42	D06X60/830	D06X60 4430LM 28,1W/830 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	28,1 W	4 430 lm	158 lm/W
42 289 43	D06X6021/830	D06X60 2120LM 13,5W/830 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	13,5 W	2 120 lm	157 lm/W
42 289 44	D06X6030/830	D06X60 3030LM 18,9W/830 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	18,9 W	3 030 lm	160 lm/W
42 289 45	D06X6033/830	D06X60 3330LM 20,8W/830 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	20,8 W	3 330 lm	160 lm/W
42 289 46	D06X6042/830	D06X60 4170LM 26,4W/830 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	26,4 W	4 170 lm	158 lm/W
42 289 47	D06X6050/830	D06X60 4990LM 32,0W/830 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	32,0 W	4 990 lm	156 lm/W
42 289 48	D06X6058/830	D06X60 5840LM 38,0W/830 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	38,0 W	5 840 lm	154 lm/W
42 022 72	D06X60ED/830	D06X60 4430LM 28,1W/830 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	28,1 W	4 430 lm	158 lm/W
42 022 73	D06X6021ED/830	D06X60 2120LM 13,5W/830 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	13,5 W	2 120 lm	157 lm/W
42 022 74	D06X6030ED/830	D06X60 3030LM 18,9W/830 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	18,9 W	3 030 lm	160 lm/W
42 022 75	D06X6033ED/830	D06X60 3330LM 20,8W/830 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	20,8 W	3 330 lm	160 lm/W
42 022 76	D06X6042ED/830	D06X60 4170LM 26,4W/830 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	26,4 W	4 170 lm	158 lm/W
42 022 77	D06X6050ED/830	D06X60 4990LM 32,0W/830 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	32,0 W	4 990 lm	156 lm/W
42 022 78	D06X6058ED/830	D06X60 5840LM 38,0W/830 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	38,0 W	5 840 lm	154 lm/W
Dora LED 600x600 - opal diffuser - 940									
42 022 37	D06X60/940	D06X60 4380LM 28,1W/940 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	28,1 W	4 380 lm	156 lm/W
42 289 49	D06X6021/940	D06X60 2090LM 13,5W/940 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	13,5 W	2 090 lm	155 lm/W
42 289 50	D06X6030/940	D06X60 2990LM 18,9W/940 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	18,9 W	2 990 lm	158 lm/W
42 289 51	D06X6033/940	D06X60 3280LM 20,8W/940 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	20,8 W	3 280 lm	158 lm/W
42 289 52	D06X6041/940	D06X60 4110LM 26,4W/940 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	26,4 W	4 110 lm	156 lm/W
42 289 53	D06X6049/940	D06X60 4930LM 32,0W/940 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	32,0 W	4 930 lm	154 lm/W
42 289 54	D06X6058/940	D06X60 5760LM 38,0W/940 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	38,0 W	5 760 lm	152 lm/W
42 022 33	D06X60ED/940	D06X60 4380LM 28,1W/940 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	28,1 W	4 380 lm	156 lm/W
42 022 79	D06X6021ED/940	D06X60 2090LM 13,5W/940 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	13,5 W	2 090 lm	155 lm/W
42 022 80	D06X6030ED/940	D06X60 2990LM 18,9W/940 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	18,9 W	2 990 lm	158 lm/W
42 022 81	D06X6033ED/940	D06X60 3280LM 20,8W/940 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	20,8 W	3 280 lm	158 lm/W
42 022 82	D06X6041ED/940	D06X60 4110LM 26,4W/940 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	26,4 W	4 110 lm	156 lm/W
42 022 83	D06X6049ED/940	D06X60 4930LM 32,0W/940 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	32,0 W	4 930 lm	154 lm/W
42 022 84	D06X6058ED/940	D06X60 5760LM 38,0W/940 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	38,0 W	5 760 lm	152 lm/W
Dora LED 600x600 - opal diffuser - 930									
42 289 55	D06X60/930	D06X60 4410LM 30,0W/930 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	30,0 W	4 410 lm	147 lm/W
42 289 56	D06X6020/930	D06X60 1980LM 13,5W/930 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	13,5 W	1 980 lm	147 lm/W
42 289 57	D06X6031/930	D06X60 3110LM 20,8W/930 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	20,8 W	3 110 lm	150 lm/W
42 289 58	D06X6034/930	D06X60 3380LM 22,7W/930 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	22,7 W	3 380 lm	149 lm/W
42 289 59	D06X6041/930	D06X60 4140LM 28,1W/930 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	28,1 W	4 140 lm	147 lm/W
42 289 60	D06X6049/930	D06X60 4930LM 34,0W/930 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	34,0 W	4 930 lm	145 lm/W
42 289 61	D06X6055/930	D06X60 5460LM 38,0W/930 O	ON/OFF	Opal	2,7 kg	595 x 595 x 33 mm	38,0 W	5 460 lm	144 lm/W
42 022 85	D06X60ED/930	D06X60 4410LM 30,0W/930 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	30,0 W	4 410 lm	147 lm/W
42 022 86	D06X6020ED/930	D06X60 1980LM 13,5W/930 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	13,5 W	1 980 lm	147 lm/W
42 022 87	D06X6031ED/930	D06X60 3110LM 20,8W/930 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	20,8 W	3 110 lm	150 lm/W
42 022 88	D06X6034ED/930	D06X60 3380LM 22,7W/930 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	22,7 W	3 380 lm	149 lm/W
42 022 89	D06X6041ED/930	D06X60 4140LM 28,1W/930 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	28,1 W	4 140 lm	147 lm/W
42 022 90	D06X6049ED/930	D06X60 4930LM 34,0W/930 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	34,0 W	4 930 lm	145 lm/W
42 022 91	D06X6055ED/930	D06X60 5460LM 38,0W/930 O DALI	DALI	Opal	2,7 kg	595 x 595 x 33 mm	38,0 W	5 460 lm	144 lm/W

© We reserve the right to changes.

E number	Type	Product name	Control	Optic	Weight	L x W x H	Power	Luminous flux	lm/W
Dora LED 300x1200 - microprismatic optics - 840									
42 289 94	D03X12M/840	D03X12M 4420LM 28,1W/840 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	28,1 W	4 420 lm	157 lm/W
42 289 95	D03X12M21/840	D03X12M 2110LM 13,5W/840 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 110 lm	156 lm/W
42 289 96	D03X12M30/840	D03X12M 3020LM 18,9W/840 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	18,9 W	3 020 lm	160 lm/W
42 289 97	D03X12M50/840	D03X12M 4980LM 32,0W/840 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	32,0 W	4 980 lm	156 lm/W
42 289 62	D03X12MED/840	D03X12M 4420LM 28,1W/840 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	28,1 W	4 420 lm	157 lm/W
42 289 63	D03X12M21ED/840	D03X12M 2110LM 13,5W/840 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 110 lm	156 lm/W
42 289 64	D03X12M30ED/840	D03X12M 3020LM 18,9W/840 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	18,9 W	3 020 lm	160 lm/W
42 289 65	D03X12M50ED/840	D03X12M 4980LM 32,0W/840 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	32,0 W	4 980 lm	156 lm/W
Dora LED 300x1200 - microprismatic optics - 830									
42 289 98	D03X12M/830	D03X12M 4450LM 30,0W/830 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	30,0 W	4 450 lm	148 lm/W
42 289 99	D03X12M20/830	D03X12M 2000LM 13,5W/830 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 000 lm	148 lm/W
42 601 02	D03X12M31/830	D03X12M 3140LM 20,8W/830 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	20,8 W	3 140 lm	151 lm/W
42 601 03	D03X12M50/830	D03X12M 4970LM 34,0W/830 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	34,0 W	4 970 lm	146 lm/W
42 289 66	D03X12MED/830	D03X12M 4450LM 30,0W/830 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	30,0 W	4 450 lm	148 lm/W
42 289 67	D03X12M20ED/830	D03X12M 2000LM 13,5W/830 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 000 lm	148 lm/W
42 289 68	D03X12M31ED/830	D03X12M 3140LM 20,8W/830 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	20,8 W	3 140 lm	151 lm/W
42 289 69	D03X12M50ED/830	D03X12M 4970LM 34,0W/830 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	34,0 W	4 970 lm	146 lm/W
Dora LED 300x1200 - microprismatic optics - 940									
42 601 05	D03X12M/940	D03X12M 4390LM 30,0W/940 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	30,0 W	4 390 lm	146 lm/W
42 601 06	D03X12M20/940	D03X12M 1970LM 13,5W/940 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	13,5 W	1 970 lm	146 lm/W
42 601 08	D03X12M30/940	D03X12M 3090LM 20,8W/940 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	20,8 W	3 090 lm	149 lm/W
42 601 09	D03X12M49/940	D03X12M 4900LM 34,0W/940 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	34,0 W	4 900 lm	144 lm/W
42 289 70	D03X12MED/940	D03X12M 4390LM 30,0W/940 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	30,0 W	4 390 lm	146 lm/W
42 289 71	D03X12M20ED/940	D03X12M 1970LM 13,5W/940 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	13,5 W	1 970 lm	146 lm/W
42 289 72	D03X12M30ED/940	D03X12M 3090LM 20,8W/940 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	20,8 W	3 090 lm	149 lm/W
42 289 73	D03X12M49ED/940	D03X12M 4900LM 34,0W/940 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	34,0 W	4 900 lm	144 lm/W
Dora LED 300x1200 - microprismatic optics - 930									
42 601 10	D03X12M/930	D03X12M 4410LM 32,0W/930 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	32,0 W	4 410 lm	138 lm/W
42 601 11	D03X12M19/930	D03X12M 1870LM 13,5W/930 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	13,5 W	1 870 lm	139 lm/W
42 601 12	D03X12M29/930	D03X12M 2930LM 20,8W/930 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	20,8 W	2 930 lm	141 lm/W
42 601 13	D03X12M49/930	D03X12M 4880LM 35,8W/930 MP	ON/OFF	Microprism	2,7 kg	295 x 1195 x 33 mm	35,8 W	4 880 lm	136 lm/W
42 289 74	D03X12MED/930	D03X12M 4410LM 32,0W/930 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	32,0 W	4 410 lm	138 lm/W
42 289 75	D03X12M19ED/930	D03X12M 1870LM 13,5W/930 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	13,5 W	1 870 lm	139 lm/W
42 289 76	D03X12M29ED/930	D03X12M 2930LM 20,8W/930 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	20,8 W	2 930 lm	141 lm/W
42 289 77	D03X12M49ED/930	D03X12M 4880LM 35,8W/930 MP DALI	DALI	Microprism	2,7 kg	295 x 1195 x 33 mm	35,8 W	4 880 lm	136 lm/W
Dora LED 300x1200 - opal diffuser - 840									
42 601 14	D03X120/840	D03X120 4410LM 26,4W/840 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	26,4 W	4 410 lm	167 lm/W
42 601 15	D03X12022/840	D03X120 2240LM 13,5W/840 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 240 lm	166 lm/W
42 601 16	D03X12032/840	D03X120 3200LM 18,9W/840 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	18,9 W	3 200 lm	169 lm/W
42 601 17	D03X12050/840	D03X120 4980LM 30,0W/840 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	30,0 W	4 980 lm	166 lm/W
42 289 78	D03X120ED/840	D03X120 4410LM 26,4W/840 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	26,4 W	4 410 lm	167 lm/W
42 289 79	D03X12022ED/840	D03X120 2240LM 13,5W/840 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 240 lm	166 lm/W
42 289 80	D03X12032ED/840	D03X120 3200LM 18,9W/840 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	18,9 W	3 200 lm	169 lm/W
42 289 81	D03X12050ED/840	D03X120 4980LM 30,0W/840 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	30,0 W	4 980 lm	166 lm/W

© We reserve the right to changes.

E number	Type	Product name	Control	Optic	Weight	L x W x H	Power	Luminous flux	lm/W
Dora LED 300x1200 - opal diffuser - 830									
42 601 18	D03X120/830	D03X120 4430LM 28,1W/830 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	28,1 W	4 430 lm	158 lm/W
42 601 19	D03X12021/830	D03X120 2120LM 13,5W/830 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 120 lm	157 lm/W
42 601 20	D03X12030/830	D03X120 3030LM 18,9W/830 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	18,9 W	3 030 lm	160 lm/W
42 601 21	D03X12050/830	D03X120 4990LM 32,0W/830 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	32,0 W	4 990 lm	156 lm/W
42 289 82	D03X120ED/830	D03X120 4430LM 28,1W/830 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	28,1 W	4 430 lm	158 lm/W
42 289 83	D03X12021ED/830	D03X120 2120LM 13,5W/830 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 120 lm	157 lm/W
42 289 84	D03X12030ED/830	D03X120 3030LM 18,9W/830 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	18,9 W	3 030 lm	160 lm/W
42 289 85	D03X12050ED/830	D03X120 4990LM 32,0W/830 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	32,0 W	4 990 lm	156 lm/W
Dora LED 300x1200 - opal diffuser - 940									
42 601 22	D03X120/940	D03X120 4380LM 28,1W/940 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	28,1 W	4 380 lm	156 lm/W
42 601 23	D03X12021/940	D03X120 2090LM 13,5W/940 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 090 lm	155 lm/W
42 601 24	D03X12030/940	D03X120 2990LM 18,9W/940 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	18,9 W	2 990 lm	158 lm/W
42 601 25	D03X12049/940	D03X120 4930LM 32,0W/940 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	32,0 W	4 930 lm	154 lm/W
42 289 86	D03X120ED/940	D03X120 4380LM 28,1W/940 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	28,1 W	4 380 lm	156 lm/W
42 289 87	D03X12021ED/940	D03X120 2090LM 13,5W/940 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	13,5 W	2 090 lm	155 lm/W
42 289 88	D03X12030ED/940	D03X120 2990LM 18,9W/940 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	18,9 W	2 990 lm	158 lm/W
42 289 89	D03X12049ED/940	D03X120 4930LM 32,0W/940 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	32,0 W	4 930 lm	154 lm/W
Dora LED 300x1200 - opal diffuser - 930									
42 601 26	D03X120/930	D03X120 4410LM 30,0W/930 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	30,0 W	4 410 lm	147 lm/W
42 601 27	D03X12020/930	D03X120 1980LM 13,5W/930 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	13,5 W	1 980 lm	147 lm/W
42 601 28	D03X12031/930	D03X120 3110LM 20,8W/930 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	20,8 W	3 110 lm	150 lm/W
42 601 29	D03X12049/930	D03X120 4930LM 34,0W/930 O	ON/OFF	Opal	2,7 kg	295 x 1195 x 33 mm	34,0 W	4 930 lm	145 lm/W
42 289 90	D03X120ED/930	D03X120 4410LM 30,0W/930 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	30,0 W	4 410 lm	147 lm/W
42 289 91	D03X12020ED/930	D03X120 1980LM 13,5W/930 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	13,5 W	1 980 lm	147 lm/W
42 289 92	D03X12031ED/930	D03X120 3110LM 20,8W/930 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	20,8 W	3 110 lm	150 lm/W
42 289 93	D03X12049ED/930	D03X120 4930LM 34,0W/930 O DALI	DALI	Opal	2,7 kg	295 x 1195 x 33 mm	34,0 W	4 930 lm	145 lm/W
Dora LED 600x1200 - 840									
42 601 31	D06X12M/840	D06X12M 8000LM 80W/840 MP	ON/OFF	Microprism	5,4 kg	595 x 1195 x 33 mm	80,0 W	8 000 lm	100 lm/W
42 601 34	D06X120/840	D06X120 8400LM 80W/840 O	ON/OFF	Opal	5,4 kg	595 x 1195 x 33 mm	80,0 W	8 400 lm	105 lm/W
42 601 46	D06X12MED/840	D06X12M 8000LM 80W/840 MP DALI	DALI	Microprism	5,4 kg	595 x 1195 x 33 mm	80,0 W	8 000 lm	100 lm/W
42 601 48	D06X120ED/840	D06X120 8400LM 80W/840 O DALI	DALI	Opal	5,4 kg	595 x 1195 x 33 mm	80,0 W	8 400 lm	105 lm/W
Dora LED 600x1200 - 830									
42 601 30	D06X12M/830	D06X12M 7200LM 80W/830 MP	ON/OFF	Microprism	5,4 kg	595 x 1195 x 33 mm	80,0 W	7 200 lm	90 lm/W
42 601 32	D06X120/830	D06X120 7600LM 80W/830 O	ON/OFF	Opal	5,4 kg	595 x 1195 x 33 mm	80,0 W	7 600 lm	95 lm/W
42 601 44	D06X12MED/830	D06X12M 7200LM 80W/830 MP DALI	DALI	Microprism	5,4 kg	595 x 1195 x 33 mm	80,0 W	7 200 lm	90 lm/W
42 601 47	D06X120ED/830	D06X120 7600LM 80W/830 O DALI	DALI	Opal	5,4 kg	595 x 1195 x 33 mm	80,0 W	7 600 lm	95 lm/W
Dora LED 300x600 - 940									
42 601 35	D03X6M/940	D03X6M 2430LM 18W/940 MP	ON/OFF	Microprism	1,4 kg	295 x 595 x 33 mm	18,0 W	2 430 lm	135 lm/W
42 601 38	D03X60/940	D03X60 2520LM 18W/940 O	ON/OFF	Opal	1,4 kg	295 x 595 x 33 mm	18,0 W	2 520 lm	140 lm/W
42 601 49	D03X6MED/940	D03X6M 2430LM 18W/940 MP DALI	DALI	Microprism	1,4 kg	295 x 595 x 33 mm	18,0 W	2 430 lm	135 lm/W
42 601 52	D03X60ED/940	D03X60 2520LM 18W/940 O DALI	DALI	Opal	1,4 kg	295 x 595 x 33 mm	18,0 W	2 520 lm	140 lm/W
Dora LED 300x600 - 930									
42 601 37	D03X6M/930	D03X6M 2250LM 18W/930 MP	ON/OFF	Microprism	1,4 kg	295 x 595 x 33 mm	18,0 W	2 250 lm	125 lm/W
42 601 40	D03X60/930	D03X60 2340LM 18W/930 O	ON/OFF	Opal	1,4 kg	295 x 595 x 33 mm	18,0 W	2 340 lm	130 lm/W
42 601 50	D03X6MED/930	D03X6M 2250LM 18W/930 MP DALI	DALI	Microprism	1,4 kg	295 x 595 x 33 mm	18,0 W	2 250 lm	125 lm/W
42 601 53	D03X60ED/930	D03X60 2340LM 18W/930 O DALI	DALI	Opal	1,4 kg	295 x 595 x 33 mm	18,0 W	2 340 lm	130 lm/W

© We reserve the right to changes.

E number	Type	Product name	Weight	L x W x H
Dora accessories				
41 174 77	DO6X6-FMS	DO6X6 FLUSH MOUNT KIT	0,7 kg	20 x 23 x 50 mm
41 174 78	DO6X12-FMS	DO6X12 FLUSH MOUNT KIT	0,1 kg	20 x 23 x 50 mm
42 022 20	RVDO6X6	RVDO6X6 SUSPENSION KIT	0,18 kg	
42 022 21	RVDO3X12	RVDO3X12 SUSPENSION KIT	0,2 kg	
42 022 22	DO6X6-KM	DO6X6-KM SURFACE KIT	1,0 kg	600 x 600 x 70 mm
42 022 23	DO3X12-KM	DO3X12-KM SURFACE KIT	1,1 kg	1200 x 300 x 70 mm
42 613 60	DL3X12-LK	DL3X12-LK mounting frame for solid ceilings	2,6 kg	1236 x 343 x 66 mm
42 606 61	DL6X6-LK	DL6X6-LK mounting frame for solid ceilings	0,2 kg	637 x 650 x 66 mm
42 175 87	DL6X6-UK30	DL6X6-UK30 embedding frame 30m, white	1,0 kg	595 x 595 x 30 mm
42 175 88	DL6X6-UKR30	DL6X6-UKR30 embedding frame with grid 30mm, white	1,2 kg	595 x 595 x 30 mm
42 175 89	DL6X6-UK54	DL6X6-UK54 embedding frame 50m, white	1,4 kg	595 x 595 x 54 mm
42 175 90	DL6X6-UKR54	DL6X6-UKR54 embedding frame with grid 50mm, white	1,7 kg	595 x 595 x 54 mm
42 613 74	DL6X6-R400	DL6X6-R400 DECORATIVE PLATE, OPENING 400mm	0,3 kg	597 x 597 x 1 mm
42 613 75	DL6X6-R500	DL6X6-R500 DECORATIVE PLATE, OPENING 500mm	0,3 kg	597 x 597 x 1 mm
42 601 55	DO6X6-HTB	DO6X6-HTB CONCEALED T-BAR BRACKET 32/38		Only cymmetrical t-bar systems
	DOTLB-38R	Dora T bar Locking bracket, 4 pcs, h=38mm R	0,1 kg	



DL6X6-UK30
embedding frame



DL6X6-UKR30
embedding frame with grid



DL6X6-UK54
embedding frame



DL6X6-UKR54
embedding frame with grid



DL3X12-LK
mounting frame for solid ceilings



DL6X6-R400
decorative plate

DO3X6



DO3X12



DO6X6



DO6X12



Luminaires per miniature circuit breaker			B10	B16	C10	C16
DO6X6, DO3X12	13,5-38W	ON/OFF	40	65	40	65
DO6X6, DO3X12	13,5W	DALI	64	103	64	103
DO6X6, DO3X12	18,9-38W	DALI	39	63	39	63
DO3X6	17,5W	ON/OFF	40	65	40	65
DO3X6	17,5W	DALI	64	103	64	103
DO6X12		ON/OFF	8	13	13	22
DO6X12		DALI	6	10	10	16

© We reserve the right to changes.

DIP Configuration - DALI / SwitchDIM





LED driver current		DO6X6MED, DO3X12MED								
		DIP-switch				/840	/830	/940	/930	
mA	W	1	2	3	4	lm	lm	lm	lm	Default
500	18.9	0	0	0	0	3020	2860	2820	2670	
550	20.8	0	1	1	0	3320	3140	3090	2930	
600	22.7	1	1	1	0	3600	3410	3360	3190	
650	24.6	0	0	0	1	3890	3680	3630	3440	
700	26.4	1	0	0	1	4160	3930	3880	3680	
750	28.1	0	1	0	1	4420	4180	4130	3910	DO6X6MED/840, DO3X12MED/840
800	30.0	1	1	0	1	4700	4450	4390	4160	DO6X6MED/830, DO6X6MED/940, DO3X12MED/940, DO3X12MED/830
850	32.0	0	0	1	1	4980	4710	4650	4410	DO6X6MED/930, DO3X12MED/930
900	34.0	1	0	1	1	5250	4970	4900	4650	
950	35.8	0	1	1	1	5510	5220	5140	4880	
1000	38.0	1	1	1	1	5830	5510	5430	5150	

LED driver current		DO6X6OED, DO3X12OED								
		DIP-switch				/840	/830	/940	/930	
mA	W	1	2	3	4	lm	lm	lm	lm	Default
500	18.9	0	0	0	0	3200	3030	2990	2830	
550	20.8	0	1	1	0	3520	3330	3280	3110	
600	22.7	1	1	1	0	3820	3610	3560	3380	
650	24.6	0	0	0	1	4120	3900	3850	3650	
700	26.4	1	0	0	1	4410	4170	4110	3900	DO6X6OED/840, DO3X12OED/840
750	28.1	0	1	0	1	4690	4430	4380	4140	DO6X6OED/830, DO6X6OED/940, DO3X12OED/940, DO3X12OED/830
800	30.0	1	1	0	1	4980	4720	4650	4410	DO6X6OED/930, DO3X12OED/930
850	32.0	0	0	1	1	5280	4990	4930	4670	
900	34.0	1	0	1	1	5570	5270	5190	4930	
950	35.8	0	1	1	1	5840	5530	5450	5170	
1000	38.0	1	1	1	1	6180	5840	5760	5460	

DIP configuration - ON/OFF





LED driver current		DO6X6M, DO3X12M								
		DIP-switch				/840	/830	/940	/930	
mA	W	1	2	3	4	lm	lm	lm	lm	Default
350	13.5	1	0	0	0	2110	2000	1970	1870	
500	18.9	0	0	1	0	3020	2860	2820	2670	
550	20.8	1	0	1	0	3320	3140	3090	2930	
600	22.7	0	1	1	0	3600	3410	3360	3190	
650	24.6	1	1	1	0	3890	3680	3630	3440	
700	26.4	0	0	0	1	4160	3930	3880	3680	
750	28.1	1	0	0	1	4420	4180	4130	3910	DO6X6M/840, DO3X12M/840
800	30.0	0	1	0	1	4700	4450	4390	4160	DO6X6M/830, DO6X6M/940, DO3X12M/940, DO3X12M/830
850	32.0	1	1	0	1	4980	4710	4650	4410	DO6X6M/930, DO3X12M/930
900	34.0	0	0	1	1	5250	4970	4900	4650	
950	35.8	0	1	1	1	5510	5220	5140	4880	
1000	38.0	1	1	1	1	5830	5510	5430	5150	

LED driver current		DO6X6O, DO3X12O								
		DIP-switch				/840	/830	/940	/930	
mA	W	1	2	3	4	lm	lm	lm	lm	Default
350	13.5	1	0	0	0	2240	2120	2090	1980	
500	18.9	0	0	1	0	3200	3030	2990	2830	
550	20.8	1	0	1	0	3520	3330	3280	3110	
600	22.7	0	1	1	0	3820	3610	3560	3380	
650	24.6	1	1	1	0	4120	3900	3850	3650	
700	26.4	0	0	0	1	4410	4170	4110	3900	DO6X6O/840, DO3X12O/840
750	28.1	1	0	0	1	4690	4430	4380	4140	DO6X6O/830, DO6X6O/940, DO3X12O/940, DO3X12O/830
800	30.0	0	1	0	1	4980	4720	4650	4410	DO6X6O/930, DO3X12O/930
850	32.0	1	1	0	1	5280	4990	4930	4670	
900	34.0	0	0	1	1	5570	5270	5190	4930	
950	35.8	0	1	1	1	5840	5530	5450	5170	
1000	38.0	1	1	1	1	6180	5840	5760	5460	

© We reserve the right to changes.