


Legrand cabling system LCS²

area distribution cords



0 517 90

0 515 03

Pack	Cat.Nos	Cords cat. 5e - RJ 45/stripped
		RJ 45 - straight stripped Clip on and off in the area distribution boxes and RJ 45 socket connection via LCS ² connector via the stripped side Cords prepared in factory, "ready for wiring" Conform to standards ISO/IEC 11801 Ed. 2.0, EN 50173-1 and TIA/EIA 568 Grey RAL 7035 Wiring in T 568 B
		U/UTP unscreened impedance 100 Ω
4	0 517 90	Length 8 m
4	0 517 91	Length 15 m
4	0 517 92	Length 20 m
		F/UTP screened impedance 100 Ω
4	0 517 93	Length 8 m
4	0 517 94	Length 15 m
4	0 517 95	Length 20 m
		Cords cat. 5e - RJ 45/RJ 45 For direct connection via RJ 45 male plug to the area distribution box and to the RJ 45 socket with copper feedthrough to ensure: - safe connection - speed and reliability of connection Grey RAL 7035
		U/UTP unscreened impedance 100 Ω
4	0 515 00	Length 8 m
4	0 515 01	Length 15 m
4	0 515 02	Length 20 m
		F/UTP unscreened impedance 100 Ω
4	0 515 03	Length 8 m
4	0 515 04	Length 15 m
4	0 515 05	Length 20 m

Legrand cabling system LCS²

feedthrough sockets - Mosaic™ Programme and Arteor



0 786 28

0 786 25

Certified as conforming to standards ISO 11801 ed. 2.0, EN 50173-1 and EIA/TIA 568

Contacts marked with 568 A and B dual colour code and numbers

Connectors with self-stripping terminals

Possibility of re-wiring in the event of error

Multidirectional cable entry

For use with area distribution boxes (see opposite), connection to boxes via RJ 45-RJ 45 dedicated cords

Used to create cat. 6A, cat. 6 and cat. 5e links in accordance with standards

2 modules

Pack	Cat.Nos	Sockets with copper feedthrough cat. 6A
		Cat. 6A STP - Mosaic Programme ○ White ● Aluminium
10	0 786 28	
10	0 786 29	
		Sockets with copper feedthrough cat. 6 Cat. 6 UTP - Mosaic Programme ○ White ● Aluminium
10	0 786 22	
10	0 786 26	
		Cat. 6 FTP - Mosaic Programme ○ White ● Aluminium
10	0 786 23	
10	0 786 27	
		Cat. 6 UTP - Arteor ○ White ● Magnesium
10	5 723 31	
10	5 728 31	
		Cat. 6 FTP - Arteor ○ White ● Magnesium
10	5 723 33	
10	5 728 33	
		Sockets with copper feedthrough cat. 5e Cat. 5e UTP - Mosaic Programme ○ White ● Aluminium
10	0 786 20	
10	0 786 24	
		Cat. 5e FTP - Mosaic Programme ○ White ● Aluminium
10	0 786 21	
10	0 786 25	
		Cat. 5e UTP - Arteor ○ White ● Magnesium
10	5 723 30	
10	5 728 30	
		Cat. 5e FTP - Arteor ○ White ● Magnesium
10	5 723 32	
10	5 728 32	