L legrand®

87045 LIMOGES Cedex
Phone : 05 55 06 87 87 – Fax : 05 55 06 88 88

Meeting room multi-outlet extensions

Number(s) : 0 535 98 – 0 546 70/72/73/99

1. Meeting room multi-outlet extensions equipped for U shaped tables layout :
- equipped with 5 to 6 x 45° 2P+E sockets for easy insertion of elbow plugs.

Power : 16A 3680W in 230V (AC)

- equipped with 3m cord (HO5VVF 3 G1.5mm²) with 2P+E plugs and with 3m cord with RJ 45 cat.6 FTP

The meeting room multi-outlet extensions offers:

- a range perfectly adapted to the needs of U shaped meeting rooms layout
- product design, aesthetic and ergonomic.
- a connection of the users with RJ45
- reliability and an optimal safety (conform to the standard NFC 61-314)

Packaging : 1

1.1 With switch number 0 546 70

For connecting up to 6 devices and networking up to 6 peripherals (computers...)

Requires the use of Ethernet 10/100 base T network cards on the peripherals for 10/100 Mbps data exchanges

Composition :

- 6 x 45° 2 P+E sockets
- 1 non manageable 10/100 base T switch 6 ports with integrated port status display
Dimensions in mm : L = 510 x l = 114 x h = 85

1. Meeting room multi-outlet extensions equipped for U shaped layout (continued) :

1.2 With non manageable switch and HD 15 + jack 3,5 socket number 0 546 72

For connecting up to 5 devices and networking up to 6 peripherals (computers,…)
One connection point with HD 15 connector and a 3.5 mm jack
Requires the use of Ethernet 10/100 base T network cards on the peripherals for 10/100 Mbps data exchanges
Composition :
- 5 x 45 ° 2 P+E sockets
- 1 10/100 base T non manageable switch 6 ports with integrated port status display
- 1 HD 15 socket + 3.5 mm jack
- 1 female VGA cord, length 0.80 m – to be used with a VGA extension
- 1 female jack 3.5 mm , length 0.80 m
Dimensions : L = 510 x l = 114 x h = 85

1.3 With non manageable switch and HDMI socket number 0 546 73

For connecting up to 5 devices and networking up to 6 peripherals (computers…)
One connection point with HDMI
Requires the use of Ethernet 10/100 base T network cards on the peripherals for 10/100 Mbps data exchanges
Composition :
- 5 x 45 2 P+E sockets
- 1 10/100 base T non manageable switch 6 ports with integrated port status display
- 1 HDMI 1.4 socket
- HDMI cord length 0.80 m
Dimensions : L = 510 x l = 114 x h = 85

1.4 Accessories

1.4.1 Fixing accessory Number 0 546 99

if L > to 400 mm use 2 x 0546 99

Allows fixing on a desk from 6 to 40 mm of depth

The product includes adhesive protections for furniture surfaces.

Material characteristics of 0 546 99 :

- Steel (painted grey)
- Polyamide
- Elastomer

Packaging : 1

1.4.2 Cable worm number 0 535 98

Very suitable solution for a safe and aesthetic protection of the cabling between desk and floor.
Packaging : 1
Length : 0.75m
Cabling capacity :
- minimum dimension of cable : 2x0,5 mm² (5mm diameter) 20 each side
- maximum dimension of cable: 5x2,5 mm² (14mm diameter) 3 each side
Material Characteristics of Nr. 0 535 98

Ring white colour : ABS + *thermoplastic polyurethane (for the membrane)*
- Fixation accessory: ABS
- Base : plastic part = EPDM
        Metal plate = FE

2. ON DEMAND

Selection of desktop multi-outlet new design

Connection
- without cable
- cord with 2P+E sockets
- cord with male connector (black or white)
- stripped cable

H05 VVF cable
Section :
- 1,5 mm²
- 2,5 mm²

Length of cable
(3,4,5 or 6 m)

End cap

The length of the unit varies depending on the quantity of functions needed.

Selection of functions

Power control functions
-   Time switch,
-   Sensor
-   Light up switch

Tamperproof socket

- 6 ports switch
- Wi-Fi

-   Reading light
-   USB charger

Power sockets
-   white
-   green
-   red
-   orange

Low current functions
-   RJ 45
-   Video
-   Audio
-   Video projector control

Compatible with protection devices :
-   RCBO (Mosaic or Arteor)

3. MATERIAL CHARACTERISTICS

Standard product or on demand, natural anodized aluminium
End caps : white ABS
Cable grip : ABS
Terminal blocks : Polypropylene
Light switch : white PC