

## Air circuit breakers DMX<sup>3</sup> 6300

5000 and 6300 A



0 289 51 + 0 288 02

Dimensions [see e-catalogue](#)  
Electrical characteristics [see e-catalogue](#)

Automatic air circuit breakers must be equipped with electronic protection unit, imperatively ordered together for factory assembly  
Please ask for DMX<sup>3</sup> order form  
Conform to IEC 60947-2

Pack	Cat.Nos
1	0 289 50   0 289 60
1	0 289 51   0 289 61

### Fixed version

Supplied with:  
- 4 auxiliary contacts: NO/NC  
- rear terminals for horizontal connection with bars  
- door sealing

#### DMX<sup>3</sup> - L 6300

Breaking capacity Icu 100 kA (415 V~)  
Frame 6300  
3P | 4P In(A)

Pack	Cat.Nos
1	0 289 52   0 289 62
1	0 289 53   0 289 63

### Draw-out version

Supplied with:  
- 4 auxiliary contacts: NO/NC  
- draw-out base and kit  
- flat rear terminals for connection with bars  
- door sealing

#### DMX<sup>3</sup> - L 6300

Breaking capacity Icu 100 kA (415 V~)  
Frame 6300  
3P | 4P In(A)

## Electronic protection units for DMX<sup>3</sup> 2500, 4000 and 6300



0 288 02

0 288 03

Dimensions [see e-catalogue](#)  
Settings and curves [see e-catalogue](#)


DMX<sup>3</sup> circuit breakers must be equipped with electronic protection units (to be ordered together for factory assembly) enabling very precise adjustments of the protection conditions, while maintaining total discrimination with downstream devices

All protection units are equipped with batteries for powering in case of mains fault or when the breaker is open or not connected


### MP4 protection units with LCD screen

Integrated LCD screen for displaying electrical values, settings and log  
Adjustment via selector switches


**LI protection unit**  
Adjustment of:  
I<sub>i</sub>, I<sub>r</sub>, t<sub>r</sub>



**LSI protection unit**  
Adjustment of:  
I<sub>sd</sub>, t<sub>sd</sub>, I<sub>r</sub>, t<sub>r</sub> and I<sub>i</sub>



**LSIG protection unit**  
Adjustment of:  
I<sub>sd</sub>, t<sub>sd</sub>, I<sub>r</sub>, t<sub>r</sub>, I<sub>i</sub>, I<sub>g</sub> and t<sub>g</sub>



### MP6 touch screen protection units

Measure and display instantaneous, maximum and average values of different electrical values and protection conditions  
Fault signalling and log

**LSI protection unit**  
Adjustment of: I<sub>sd</sub>, t<sub>sd</sub>, I<sub>r</sub>, t<sub>r</sub> and I<sub>i</sub>

**LSIG protection unit**  
Adjustment of: I<sub>sd</sub>, t<sub>sd</sub>, I<sub>r</sub>, t<sub>r</sub>, I<sub>i</sub>, I<sub>g</sub> and t<sub>g</sub>

### Accessories for electronic protection units

1 | 0 288 05<sup>1</sup> Communication option for DMX<sup>3</sup> electronic protection units

1 | 0 288 06 24 V DC external auxiliary power supply

1 | 0 288 10<sup>1</sup> External neutral for DMX<sup>3</sup> 6300

1 | 0 288 11<sup>1</sup> External neutral for DMX<sup>3</sup> 2500 and 4000

1 | 0 288 12<sup>1</sup> Module programmable output

1: Optional accessories, to be ordered when ordering electronic protection unit and DMX<sup>3</sup> air circuit breakers for factory assembly

Dimensions of DMX<sup>3</sup> range,  
[see e-catalogue](#)

