

Arteor™

lighting control, emergency push-buttons



5 720 55



5 723 63

Support frame and plate selection charts **p. 480-487**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 476) and plates (p. 480 to 487)

Pack	Cat.Nos	Time delay switches
1	5 720 55	<p>Interference suppression conforming to standard EN 55022 For timer control of a circuit with the following loads: - 1000 W incandescent and halogen 230 V~ - 2300 W resistive (heating) - 400 VA fluorescent and ELV halogen Adjustable from 25 s to 15 min It is possible to install a number of timer switches in parallel on the same circuit With integrated LED 2-wire installation in box min. depth 40 mm 2 modules</p> <p> White Magnesium</p>
1	5 740 84	

Pack	Cat.Nos	Single pole latching relays 10 A - 250 V~
1	5 722 27	<p>Used to bring functions with low breaking capacity close to the application Resistive: 3000 W Incandescent: 1800 W LV halogen: 1800 W Fluorescent: 400 VA Motors (roller blind type): 530 W 2 modules</p> <p> White Magnesium</p>
1	5 727 27	

Pack	Cat.Nos	Emergency stop mushroom head push-buttons 10 A - 250 V~
1	5 723 63	<p>N/O + N/C 2 modules</p> <p>With key Unlock with RONIS key no. 601 Yellow/red</p> <p>1/4 turn 1/4 turn unlocking Yellow/red</p>
1	5 723 62	

Arteor™

double pole switches, cooker control unit



5 720 87



5 720 88

Support frame and plate selection charts **p. 480-487**

Mechanisms supplied with rocker plates, to be equipped with plate (p. 476)
Support frame not needed

Pack	Cat.Nos	Double pole switches 40 A - 250 V~
5	5 720 81	<p>Conform to EN 60669-1: 2000 and SANS 164-1 Captive terminal screws For flush-mounting box to be min. 48 mm deep Use US plate 4" x 4" - 2 modules</p> <p>Double pole switch White Magnesium</p>
5	5 725 81	
5	5 720 82	<p>Double pole switch + neon White Magnesium</p>
5	5 725 82	

Pack	Cat.Nos	Double pole switches 45 A - 250 V~
5	5 720 80	<p>Conform to EN 60669-1: 2000 Captive terminal screws For flush-mounting box to be min. 48 mm deep</p> <p>Double pole switch + neon - 2 gang Use BS plate 3 modules White Magnesium</p>
5	5 725 80	
5	5 720 87	<p>Double pole switch + neon - 1 gang Use BS plate 2 modules White Magnesium</p>
5	5 725 87	

Pack	Cat.Nos	Cooker control unit 250 V~
5	5 720 88	<p>Conform to BS 4177: 1992 45 A double pole switch + 13 A double pole switched socket outlet Use special plate Cat. No 5 751 50 White</p>