



5 721 39 + 5 751 70

Pack	Cat.Nos	Multistandard switched socket outlets 16 A - 250 V \sim / 15 A - 127 V \sim with USB charger
1	5 721 38	Mechanism supplied with rocker plate, to be equipped with special plate Support frame not needed Shuttered for child safety USB charger conform to IEC 60950-1 2P+E - 1 gang USB Type-A 2,4 A - 5 V \equiv - 12 W Consumption in passive mode < 0.08 W ○ White ● Magnesium
1	5 726 38	
1	5 721 39	2 x 2P+E - 2 gang USB Type-A + Type-C™ 3 A - 5 V \equiv - 15 W Consumption in passive mode < 0.08 W ○ White ● Magnesium
1	5 726 39	

Pack	Cat.Nos	Special plates for Arteor multistandard socket outlets with USB charger
5	5 751 10	For 1 gang switched mechanism ○ Neutral - White
1	5 751 16	● Brushed Metal - Stainless Steel
5	5 751 70	For 2 gang switched mechanism ○ Neutral - White
1	5 751 76	● Brushed Metal - Stainless Steel



5 721 23

5 721 35

5 721 10

 Support frame and plate selection charts **p. 480-487**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 476) and plates (p. 480 to 487)

Pack	Cat.Nos	Multistandard socket outlets
10	5 721 23	2P+E unswitched - shuttered for child safety - 2 modules ○ White ● Magnesium ● Champagne ● Alu
10	5 726 23	
10	5 700 42	
10	5 710 42	
5	5 721 35	2P+E switched - shuttered for child safety - 3 modules ○ White ● Magnesium
5	5 726 35	
		British standard socket outlets Shuttered for child safety ASTA licence Conform to BS 1363 Part 2 Use special plates (p. 480-481)
5	5 721 32	2P+E switched - 15 A Conform to BS 546 3 modules ○ White ● Magnesium ● Champagne ● Alu
5	5 726 32	
5	5 700 45	
5	5 710 45	
10	5 721 11	2P+E - 13 A Conform to BS 1363 Part 2 ASTA licence 2 modules ○ White ● Magnesium ● Champagne ● Alu
10	5 726 11	
10	5 700 38	
10	5 710 38	
5	5 721 30	2P+E switched - 13 A Conform to BS 1363 Part 2 ASTA licence 3 modules ○ White ● Magnesium ● Red dedicated non standard pin ● Champagne ● Alu
5	5 726 30	
5	5 724 67	
5	5 700 44	
5	5 710 44	
10	5 721 10	2P+E - 5 A Conform to BS 546 2 modules ○ White ● Magnesium
10	5 726 10	