

Forms of separation equipment for XL³ 4000 and 6300

Designation	Complementary information	Forms of separation and type of connection (terminals)								Forms of separation and type of connection (terminals)													
		2a		2b						3a		3b			4a			4b					
		rear terminals	front terminals	rear terminals	front terminals	rear terminals	725 mm	975 mm	725 mm	975 mm	rear terminals	front terminals	rear terminals	front terminals	rear terminals	front terminals	rear terminals	front terminals	rear terminals				
For enclosures / cable sleeves depth :	725 mm	975 mm	475 mm	725 mm	975 mm	725 mm	975 mm			725 mm	975 mm	475 mm	725 mm	975 mm	725 mm	975 mm	475 mm	725 mm	975 mm	725 mm	975 mm		
Top or bottom horizontal separation kit	width 24 modules	0 208 91									0 208 91			0 208 91				0 208 91			0 208 91		
	width 36 modules	0 208 99									0 208 99			0 208 99				0 208 99			0 208 99		
Front panel partitioning DMX ³	width 24 modules	0 208 08								0 208 08													
	width 36 modules	0 208 09								0 208 09													
Front panel side partitioning										0 208 68				0 208 68								0 208 68	
Horizontal partitioning for functional units	width 24 modules							0 208 92		0 208 92			0 208 92		0 208 92			0 208 92			0 208 92		
	width 36 modules							0 205 92		0 205 92			0 205 92		0 205 92			0 205 92			0 205 92		
Kit for vertical separation between enclosure and cable sleeve	for enclosure			0 208 27	0 208 28	0 208 29						0 208 27	0 208 28	0 208 29				0 208 27	0 208 28	0 208 29			
Kit for vertical separation between internal cable sleeve and external cable sleeve	for enclosure			0 208 37	0 205 38	0 205 39						0 208 37	0 208 38	0 208 39				0 208 37	0 208 38	0 208 39			
L-shaped separation kit for horizontal busbars 1600 A max.	for enclosure			0 205 36								0 205 36						0 205 36					
U-shaped separation kit for horizontal busbars 1600 A max.	for enclosure				0 205 37								0 205 37						0 205 37				
L-shaped separation kit for horizontal busbars 4000 A max.	for enclosure				0 205 38								0 205 38						0 205 38				
U-shaped separation kit for horizontal busbars 4000 A max.	for enclosure					0 205 39								0 205 39						0 205 39			
U-shaped separation kit for horizontal busbars 6300 A max.	for XL ³ 6300 enclosures				0 211 47									0 211 47				0 211 47					
U-shaped separation kit for horizontal busbars 1600 A max.	for internal cable sleeves			0 208 70	0 208 71							0 208 70	0 208 71					0 208 70	0 208 71				
U-shaped separation kit for horizontal busbars 4000 A max.	for internal cable sleeves				0 208 72	0 208 76							0 208 72	0 208 76					0 208 72	0 208 76			
U-shaped separation kit for horizontal busbars 1600 A max.	for external cable sleeves			0 208 73	0 208 74							0 208 73	0 208 74					0 208 73	0 208 74				
U-shaped separation kit for horizontal busbars 4000 A max.	for external cable sleeves				0 208 75	0 208 86							0 208 75	0 208 86					0 208 75	0 208 86			
Side vertical divider for DPX ³ 1600					0 205 96								0 205 96						0 205 96				
Side partition with and caps for functional units separation	height 200 mm													0 205 97					0 205 97				
	height 300 mm													0 205 98					0 205 98				
	height 400 mm													0 205 99					0 205 99				
Vertical partitioning for rear busbars	for enclosure					0 208 48	0 208 49							0 208 48	0 208 49								
Partitioning for rear busbars	height 200 mm							0 208 77							0 208 77								
	height 300 mm							0 208 78							0 208 78								
	height 400 mm							0 208 79							0 208 79								
Horizontal busbar partitioning	for enclosure					0 208 93	0208 94							0 208 93	0 208 94						0 208 94		
Rear vertical partitioning															0 208 69						0 208 69		
DPX ³ compartment kit	height 200 mm																					0 208 87	
	height 300 mm																					0 208 88	
	height 400 mm																					0 208 89	
Partitioning for cell without horizontal busbars	to close last DPX compartment																					0 208 95	
Bottom busbar area closure																						0 208 96	
Rear partitioning divider for space compartment																						0 208 97	
DMX ³ 1600, compartment kit	for cables sleeve	0 210 94	0 210 95		0 210 94	0 210 95	0 210 94	0 210 95		0 210 94	0 210 95		0 210 94	0 210 95	0 210 94	0 210 95		0 210 94	0 210 95	0 210 94	0 210 95	0 210 94	0 210 95
	width 24 modules for enclosure	0 210 96	0 210 97		0 210 96	0 210 97	0 210 96	0 210 97		0 210 96	0 210 97		0 210 96	0 210 97	0 210 96	0 210 97		0 210 96	0 210 97	0 210 96	0 210 97	0 210 96	0 210 97
	width 36 modules for enclosure	0 210 98	0 210 99		0 210 98	0 210 99	0 210 98	0 210 99		0 210 98	0 210 99		0 210 98	0 210 99	0 210 98	0 210 99		0 210 98	0 210 99	0 210 98	0 210 99	0 210 98	0 210 99
DMX ³ 2500/4000, compartment kit	width 24 modules for enclosure				0 208 02	0 208 18	0 208 02	0 208 18					0 208 02	0 208 18	0 208 02	0 208 18		0 208 02	0 208 18	0 208 02	0 208 18	0 208 02	0 208 18
	width 36 modules for enclosure				0 208 03	0 208 19	0 208 03	0 208 19					0 208 03	0 208 19	0 208 03	0 208 19		0 208 03	0 208 19	0 208 03	0 208 19	0 208 03	0 208 19
DMX ³ 2500/4000, compartment kit	for XL ³ 6300 enclosures				0 211 46		0 211 46						0 211 46		0 211 46			0 211 46				0 211 46	
DMX ³ 6300, kit for horizontal separation	for XL ³ 6300 enclosures				0 211 49		0 211 49							0 211 49		0 211 49			0 211 49				0 211 49