


# Niloé™

## radio switches and roller blind controls








6 651 05

6 651 06

6 651 10

Mechanisms equipped with cover plates and support frames  
To be equipped with plates (p. 539)

Pack	Cat.Nos	Radio switches
1	6 651 05	<b>Centralized control unit - wireless transmitter switches</b> Surface-mounting or within a flush-mounting box No wiring required Powered by 3V CR 2032 lithium batteries, supplied Enables you: ○ White - single switch - to control one Radio receiver switch or a group of Radio receiver switches - to do a two-way switch without wiring 
1	6 651 06	○ White - 2-gang switch Enables you to control two Radio receiver switches or two groups of Radio receiver switches 
1	0 883 06	<b>Micromodule receiver switch 300 W</b> Enables you: - to improve an existing installation by adding control points without damage to the walls - to control LED, fluocompact, halogen and incandescent lamps as well as electronic transformers To be installed near the lamp with neutral, with Cat.No 0 306 54 (plug-in ceiling rose), for example Must be mounted with wireless switches Cat.Nos 6 651 05/06 Phase/neutral power supply 
<b>Radio roller blind controls</b>		
1	6 651 10	<b>Centralized control unit - wireless transmitter switch</b> ○ White Allows you to raise/lower/stop one or a group of individual radio receiver roller blind switches 
1	6 651 12	<b>Individual unit - receiver switch</b> ○ White For direct motor control (4-wire) Phase/neutral power supply Preset function integrated into the switch 

# Niloé™






## 2P and German standard socket outlets



7 645 29

7 645 44

Mechanisms supplied with cover plates and support frames  
To be equipped with plates (p. 539)  
Fixing with screws or claws (supplied)

Pack	Cat.Nos	2P socket outlets with safety shutters
20	7 645 38	Screw terminals ○ White ● Ivory 
20	7 646 38	
<b>German standard socket outlets with safety shutters</b>		
20	7 645 29	<b>2P+E - screw terminals</b> ○ White ● Ivory 
20	7 646 29	
10	7 645 32	<b>2P+E with flap cover - screw terminals</b> ○ White ● Ivory 
10	7 646 32	
10	7 645 31	<b>2P+E with flap cover - IP 44 - screw terminals</b> To be equipped with standard plates ○ White ● Ivory 
10	7 646 31	
10	7 645 44	<b>2 x 2P+E - compact - screw terminals</b> Supplied complete with plate Installation in 1 gang flush-mounting box Allow you to replace 1 socket with 2 sockets without changing the flush-mounting box Screw-mounting ○ White ● Ivory 
10	7 646 44	