

## Belanko™ colours

socket outlets (continued)



6 173 69

Material: Thermoplastic with paint satin finish  
Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)  
Supplied with 2 screws M3.5 for BS boxes

### Pack Cat.Nos Euro/US socket outlets - 10 A - 250 V~ / 15 A - 127 V~

10 6 173 61  
10 6 174 61  
**1 gang - 2P + 10 Ax switch**  
● Dark grey  
● Brown



10 6 173 62  
10 6 174 62  
**1 gang - 2 x 2P**  
● Dark grey  
● Brown



10 6 173 64  
10 6 174 64  
**1 gang - 2 x 2P+E**  
● Dark grey  
● Brown



### 10 6 173 56 10 6 174 56 German Standard socket outlet 16 A - 250 V~

10 6 173 56  
10 6 174 56  
**1 gang - 2P+E with shutters for child protection**  
● Dark grey  
● Brown



### 10 6 173 67 10 6 174 67 Multistandard switched socket outlet

10 6 173 67  
10 6 174 67  
**1 gang**  
● Dark grey  
● Brown



5 6 173 69  
5 6 174 69  
**2 gang**  
● Dark grey  
● Brown



### 1 6 173 59 1 6 174 59 Multistandard switched socket outlets 16 A 250 V~ / 15 A - 127 V~ with USB charger

Shuttered for child safety  
USB charger conform to IEC 60950-1

**1 gang - 2P+E**  
USB Type-A 2.4 A - 5 V<sub>DC</sub> - 12 W  
Consumption in passive mode < 0.08 W

1 6 173 59  
1 6 174 59  
● Dark grey  
● Brown



**2 gang - 2 x 2P+E**  
USB Type-A + Type-C™ 3 A - 5 V<sub>DC</sub> - 15 W  
Consumption in passive mode < 0.08 W

1 6 173 49  
1 6 174 49  
● Dark grey  
● Brown



## Belanko™ colours

fused connection units, cable outlets and blanking plates



6 173 86

### Pack Cat.Nos Fused connection units 13 A

10 6 173 80  
10 6 174 80  
Conform to BS 1363-4  
**Unswitched + cord outlet**

● Dark grey  
● Brown



10 6 173 81  
10 6 174 81  
**Switched + cord outlet**

● Dark grey  
● Brown



10 6 173 82  
10 6 174 82  
**Switched + neon + cord outlet**

● Dark grey  
● Brown



### Cable outlets

Conform to BS 5733  
**20 A - 250 V~**

10 6 173 85  
10 6 174 85  
● Dark grey  
● Brown



10 6 173 86  
10 6 174 86  
**45 A - 250 V~**

● Dark grey  
● Brown



### Blanking plates

Conform to BS 5733

10 6 173 28  
10 6 174 28  
**1 gang**  
● Dark grey  
● Brown



5 6 173 29  
5 6 174 29  
**2 gang**  
● Dark grey  
● Brown



### Arteor Adaptor

10 6 173 32  
**1 gang**  
● Dark grey

