

## Mallia™ - British standard socket outlets and fused connection units - customisable colours



2 833 42

Plate selection charts p. 577

Painted polycarbonate front cover  
Compact mechanism for greater wiring space  
Supplied with 2 screws, M 3.5 for BS boxes  
All sockets integrate child protection  
To be equipped with plates  
Dim.: 86 x 86 mm

| Pack | Cat.Nos  | British standard socket outlets 5 A - 250 V~ |
|------|----------|----------------------------------------------|
|      |          | Conform to BS 546                            |
|      |          | <b>1 gang switched</b>                       |
| 5    | 2 831 32 | Silver                                       |
| 5    | 2 833 32 | Pearl                                        |
| 5    | 2 835 32 | Dark Silver                                  |
| 5    | 2 839 32 | Champagne                                    |
| 5    | 2 821 32 | Matt Black                                   |
|      |          | <b>13 A fused connection units</b>           |
|      |          | Conform to BS 1363: Part 4                   |
|      |          | <b>Unswitched</b>                            |
| 5    | 2 831 40 | Silver                                       |
| 5    | 2 833 40 | Pearl                                        |
| 5    | 2 835 40 | Dark Silver                                  |
| 5    | 2 839 40 | Champagne                                    |
| 5    | 2 821 40 | Matt Black                                   |
|      |          | <b>Switched</b>                              |
| 5    | 2 831 41 | Silver                                       |
| 5    | 2 833 41 | Pearl                                        |
| 5    | 2 835 41 | Dark Silver                                  |
|      |          | <b>Switched with red LED power indicator</b> |
| 5    | 2 831 42 | Silver                                       |
| 5    | 2 833 42 | Pearl                                        |
| 5    | 2 835 42 | Dark Silver                                  |
| 5    | 2 839 42 | Champagne                                    |

## Mallia™ - Euro-US and German standard socket outlets customisable colours



2 835 02

Plate selection charts p. 577

Painted polycarbonate front cover  
Compact mechanism for greater wiring space  
Supplied with 2 screws M 3.5 for BS boxes  
All sockets integrate child protection  
To be equipped with plates  
Dim.: 86 x 86 mm

| Pack | Cat.Nos  | Euro-US standard socket outlets 16 A - 250 V~       |
|------|----------|-----------------------------------------------------|
|      |          | <b>2P - 1 gang + 10 A switch</b>                    |
| 5    | 2 831 01 | Silver                                              |
| 5    | 2 833 01 | Pearl                                               |
| 5    | 2 835 01 | Dark Silver                                         |
|      |          | <b>2P - 2 gang (separated connection)</b>           |
| 5    | 2 831 02 | Silver                                              |
| 5    | 2 833 02 | Pearl                                               |
| 5    | 2 835 02 | Dark Silver                                         |
|      |          | <b>2P+E - 1 gang</b>                                |
| 5    | 2 831 03 | Silver                                              |
| 5    | 2 833 03 | Pearl                                               |
| 5    | 2 835 03 | Dark Silver                                         |
| 5    | 2 839 03 | Champagne                                           |
| 5    | 2 821 03 | Matt Black                                          |
|      |          | <b>2P+E - 2 gang</b>                                |
| 5    | 2 831 04 | Silver                                              |
| 5    | 2 833 04 | Pearl                                               |
| 5    | 2 835 04 | Dark Silver                                         |
| 5    | 2 839 04 | Champagne                                           |
| 5    | 2 821 04 | Matt Black                                          |
|      |          | <b>German standard socket outlets 16 A - 250 V~</b> |
|      |          | <b>2P+E - 1 gang</b>                                |
| 5    | 2 831 26 | Silver                                              |
| 5    | 2 833 26 | Pearl                                               |
| 5    | 2 835 26 | Dark Silver                                         |
| 5    | 2 821 26 | Matt Black                                          |