

Valena™ IN'MATIC mechanisms

audio/video and USB data sockets



7 547 15 + 7 544 21
(Valena Allure - White mirror)



7 531 75 + 7 541 31
(Valena Life Aluminium)



7 531 70 + 7 541 21
(Valena Life - Link)



7 530 75 + 7 547 25 + 7 555 41
(Valena Allure - White glass)



7 531 73 + 7 540 91
(Valena Life - Adria)

Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
To be equipped with Valena Life or Valena Allure cover plates and plates
Supplied with mounted dust protection transparent shield. Packaged in boxes

Pack	Cat.Nos	Audio and video sockets
		HDMI type A sockets
		Used to transmit high-definition digital audio/video streams between a source (computer, Blu-ray player) and a compatible receiver (TV, video projector)
		Screw-type sockets HDMI 1.3
		Supplied with cover plate
1	7 531 71	<input type="checkbox"/> White Valena Life
1	7 532 71	<input type="checkbox"/> Ivory Valena Life
1	7 533 71	<input type="checkbox"/> Aluminium Valena Life
1	7 547 15	<input type="radio"/> White Valena Allure
1	7 547 16	<input type="radio"/> Ivory Valena Allure
1	7 547 17	<input type="radio"/> Aluminium Valena Allure
		Screw-type sockets HDMI 1.4
		Equipped with cord, length 15 cm
1	7 531 75	<input type="checkbox"/> White Valena Life
1	7 532 75	<input type="checkbox"/> Ivory Valena Life
1	7 533 75	<input type="checkbox"/> Aluminium Valena Life
1	7 551 65	<input type="radio"/> White Valena Allure
1	7 551 66	<input type="radio"/> Ivory Valena Allure
1	7 551 67	<input type="radio"/> Aluminium Valena Allure
		HD 15 + 3.5 mm Jack sockets
		Supplied with cover plate
		Used to transmit analogue audio/video streams between a source (computer) and a compatible receiver (TV, video projector)
		Video resolution VGA - UXGA
		HD 15 female socket + 3.5 mm jack socket (screwed)
1	7 531 70	<input type="checkbox"/> White Valena Life
1	7 532 70	<input type="checkbox"/> Ivory Valena Life
1	7 533 70	<input type="checkbox"/> Aluminium Valena Life
1	7 547 05	<input type="radio"/> White Valena Allure
1	7 547 06	<input type="radio"/> Ivory Valena Allure
1	7 547 07	<input type="radio"/> Aluminium Valena Allure
		Triple RCA socket
1	7 530 75	For the composite video and stereo audio connection of any amplifier, DVD drive, camera...
		Female USB data sockets - for data transfer
1	7 530 82	Preterminated USB 3.0. Equipped with a 15 cm cord Used to bring connections closer to the user For connecting USB devices (scanner-printer, external hard disk) Max. cable length: 5 m. Recommended cable: USB A

Pack	Cat.Nos	Loudspeaker sockets
5	7 530 72	4 mm ² terminals Single socket
5	7 530 78	Double socket
		Audio sockets
		Supplied with cover plate For the stereo connection of any peripheral, microphone, mixing console
		XLR 3-pole female sockets
1	7 531 73	<input type="checkbox"/> White Valena Life
1	7 532 73	<input type="checkbox"/> Ivory Valena Life
1	7 533 73	<input type="checkbox"/> Aluminium Valena Life
1	7 547 35	<input type="radio"/> White Valena Allure
1	7 547 36	<input type="radio"/> Ivory Valena Allure
1	7 547 37	<input type="radio"/> Aluminium Valena Allure
		XLR 3-pole male sockets
1	7 531 74	<input type="checkbox"/> White Valena Life
1	7 532 74	<input type="checkbox"/> Ivory Valena Life
1	7 533 74	<input type="checkbox"/> Aluminium Valena Life
1	7 547 45	<input type="radio"/> White Valena Allure
1	7 547 46	<input type="radio"/> Ivory Valena Allure
1	7 547 47	<input type="radio"/> Aluminium Valena Allure