




Valena™ Life

cover plate selection charts (continued)

Functions	VALENA IN'MATIC™ MECHANISMS	VALENA™ LIFE COVER PLATES		
		White 	Ivory 	Aluminium 
DIMMERS 240 V~ - 50 HZ				
Rotary dimmer without neutral	7 520 60	7 548 80	7 548 81	7 548 82
Universal dimmer without neutral	7 520 62	7 548 90	7 548 91	7 548 92
Dimmer, with neutral, for 1-10 V ballast	7 520 67			
MOTION SENSORS				
Motion sensor without neutral	7 520 70	7 548 84	7 548 93	7 548 94
Motion sensor with neutral	7 520 73			
Motion sensor without neutral, with override		7 521 72 ⁽¹⁾	7 522 72 ⁽¹⁾	7 523 72 ⁽¹⁾
ROLLER BLIND CONTROL				
Roller blind switch 10 AX - 250 V~	7 520 29	7 551 40	7 551 41	7 551 42
Roller blind push-button 6 A 250 V~	7 520 30			
KEYCARD SWITCHES				
Electronic card-operated switch	7 520 25	7 551 60	7 551 61	7 551 62
THERMOSTATS				
Electronic room thermostat		7 521 33 ⁽¹⁾	7 522 33 ⁽¹⁾	7 523 33 ⁽¹⁾
Floor heating thermostat		7 521 34 ⁽¹⁾	7 522 34 ⁽¹⁾	7 523 34 ⁽¹⁾
STAR TV-R-SAT SOCKETS				
TV-R-SAT socket	7 530 52	7 547 90	7 547 91	7 547 92
TV-R-SAT-SAT socket	7 530 56	7 548 10	7 548 11	7 548 12
TV-SAT socket	7 530 57	7 548 20	7 548 21	7 548 22
TV-R-SAT 30 mm socket cover	For TV sockets with 2 or 3 holes (breakable middle space)	7 548 00	7 548 01	7 548 02
STAR TV SOCKET				
Male TV socket	7 530 51	7 547 60	7 547 61	7 547 62
"F" type TV socket	7 530 50			
STAR TV + RJ 45 SOCKET				
TV SOCKET 0-2400 MHz + RJ45 Cat. 6 UTP	7 530 55	7 548 30	7 548 31	7 548 32
PASSTHROUGH SOCKETS				
Male TV socket	7 530 61	7 547 60	7 547 61	7 547 62
TV-R socket	7 530 63	7 547 80	7 547 81	7 547 82
TV-R-SAT socket	7 530 65	7 547 90	7 547 91	7 547 92
TV-SAT socket	7 530 71	7 548 20	7 548 21	7 548 22
TERMINAL SOCKETS				
Male TV socket	7 530 60	7 547 60	7 547 61	7 547 62
TV-R socket	7 530 62	7 547 80	7 547 81	7 547 82
TV-R-SAT socket	7 530 64	7 547 90	7 547 91	7 547 92
TV-SAT socket	7 530 59	7 548 20	7 548 21	7 548 22

1: Supplied with mechanism