

Mallia™

single pole switches - customisable colours



2 838 00



2 830 02



2 820 04



2 830 12 + 2 819 98



2 834 16 + 2 819 97

Plate selection charts p. 577

Conform to BS EN 60669-1. Painted polycarbonate front cover
Compact mechanism for greater wiring space
Supplied with 2 screws M 3.5 for BS boxes. To be equipped with plates. Dim.: 86 x 86 mm

Pack	Cat.Nos	Single pole standard switches 10 AX - 250 V~
5	2 830 00	1 gang - 1-way switch
5	2 832 00	● Silver
5	2 834 00	● Pearl
5	2 838 00	● Dark Silver
5	2 820 00	● Champagne
5	2 820 00	● Matt Black
5	2 830 01	1 gang - 2-way switch
5	2 832 01	● Silver
5	2 834 01	● Pearl
5	2 838 01	● Dark Silver
5	2 820 01	● Champagne
5	2 820 01	● Matt Black
4	2 830 08	1 gang - intermediate switch
4	2 832 08	● Silver
4	2 834 08	● Pearl
4	2 838 08	● Dark Silver
4	2 820 08	● Champagne
4	2 820 08	● Matt Black
5	2 830 02	2 gang - 1-way switch
5	2 832 02	● Silver
5	2 834 02	● Pearl
5	2 838 02	● Dark Silver
5	2 820 02	● Champagne
5	2 820 02	● Matt Black
5	2 830 03	2 gang - 2-way switch
5	2 832 03	● Silver
5	2 834 03	● Pearl
5	2 838 03	● Dark Silver
5	2 820 03	● Champagne
5	2 820 03	● Matt Black
5	2 830 04	3 gang - 1-way switch
5	2 832 04	● Silver
5	2 834 04	● Pearl
5	2 838 04	● Dark Silver
5	2 820 04	● Champagne
5	2 820 04	● Matt Black
5	2 830 05	3 gang - 2-way switch
5	2 832 05	● Silver
5	2 834 05	● Pearl
5	2 838 05	● Dark Silver
5	2 820 05	● Champagne
5	2 820 05	● Matt Black
5	2 830 06	4 gang - 1-way switch
5	2 832 06	● Silver
5	2 834 06	● Pearl
5	2 838 06	● Dark Silver
5	2 820 06	● Champagne
5	2 820 06	● Matt Black
5	2 830 07	4 gang - 2-way switch
5	2 832 07	● Silver
5	2 834 07	● Pearl
5	2 838 07	● Dark Silver
5	2 820 07	● Champagne
5	2 820 07	● Matt Black

Pack	Cat.Nos	Single pole illuminated switches 10 AX - 250 V~
		Transparent phosphorescent lens To be equipped with green or red LED according to the need: indicator or locator (p. 576) The LED is not supplied
5	2 830 10	1 gang - 1-way switch
5	2 832 10	● Silver
5	2 834 10	● Pearl
5	2 834 10	● Dark Silver
5	2 830 11	1 gang - 2-way switch
5	2 832 11	● Silver
5	2 834 11	● Pearl
5	2 834 11	● Dark Silver
4	2 830 09	1 gang - intermediate switch
4	2 832 09	● Silver
4	2 834 09	● Pearl
4	2 834 09	● Dark Silver
5	2 830 12	2 gang - 1-way switch
5	2 832 12	● Silver
5	2 834 12	● Pearl
5	2 834 12	● Dark Silver
5	2 830 13	2 gang - 2-way switch
5	2 832 13	● Silver
5	2 834 13	● Pearl
5	2 834 13	● Dark Silver
5	2 830 14	3 gang - 1-way switch
5	2 832 14	● Silver
5	2 834 14	● Pearl
5	2 834 14	● Dark Silver
5	2 830 15	3 gang - 2-way switch
5	2 832 15	● Silver
5	2 834 15	● Pearl
5	2 834 15	● Dark Silver
5	2 830 16	4 gang - 1-way switch
5	2 832 16	● Silver
5	2 834 16	● Pearl
5	2 834 16	● Dark Silver
5	2 830 17	4 gang - 2-way switch
5	2 832 17	● Silver
5	2 834 17	● Pearl
5	2 834 17	● Dark Silver