

Audio/video system

audio/video sockets (continued)



0 792 55



0 787 60



0 787 50



0 787 76

Pack	Cat.Nos		Jack sockets 3.5 mm
			3.5 mm Jack connectors can be used to create audio links
			Preterminated sockets - 1 module Equipped with cord, length 15 cm
1	Mosaic 0 787 79	Arteor 5 720 91	<ul style="list-style-type: none"> ○ White ● Alu ● Magnesium
1	0 793 79		
1		5 725 91	
			4 screw-type female 3.5 mm Jack socket - 1 module
1	0 787 64	5 722 74	<ul style="list-style-type: none"> ○ White ● Alu ● Magnesium
1	0 792 64		
1		5 727 74	
			Solder-type female 3.5 mm Jack socket - 1 module
1	0 787 73	5 722 78	<ul style="list-style-type: none"> ○ White ● Magnesium
1		5 727 78	

Pack	Cat.Nos		Female 2 RCA sockets
			Provide the stereo audio link for any peripheral device such as a DVD drive, camera, video recorder 1 module
			Preterminated Equipped with a 15 cm cord
1	Mosaic 0 787 47	Arteor 5 720 92	<ul style="list-style-type: none"> ○ White ● Magnesium
1		5 725 92	
			Connection via screw terminals
1	0 787 53	5 722 72	<ul style="list-style-type: none"> ○ White ● Magnesium
1		5 727 72	

Pack	Cat.Nos		Female 3 RCA sockets
			Provide the composite video and stereo audio links for any peripheral device such as a DVD drive, camera, video recorder, videoconferencing, etc 1 module
			Connection via screw terminals
1	Mosaic 0 787 54	Arteor 5 722 73	<ul style="list-style-type: none"> ○ White ● Alu ● Magnesium
1	0 792 54		
1		5 727 73	

Pack	Cat.Nos		3-pole XLR sockets
			Provide the stereo link for microphone, amplifier, mixing console, etc. Recommended cable: 1 audio pair 0.14 mm ² to 0.5 mm ² shielded Max. cable length: 50 m (without amplifier) 2 modules
1	Mosaic 0 787 55	Arteor 5 722 83	<ul style="list-style-type: none"> ○ White - Fast screw connection female ● Alu - Fast screw connection female ● Magnesium - Fast screw connection female
1	0 792 55		
1		5 727 83	
1	0 787 56	5 722 77	<ul style="list-style-type: none"> ○ White - Fast screw connection male ● Magnesium - Fast screw connection male
1		5 727 77	

Pack	Cat.Nos		4-pole Speakon
			Used to connect power enclosures Recommended cable: 2 audio pairs 4 mm ² Max. cable length: 50 m (without amplifier) 2 modules
1	Mosaic 0 787 60		<ul style="list-style-type: none"> ○ White

Pack	Cat.Nos		Loudspeaker sockets
			Terminal 4 mm ²
10	Mosaic 0 787 51	Arteor 5 722 80	<ul style="list-style-type: none"> ○ White - 2 modules ● Magnesium - 2 modules
10		5 727 80	
10	0 787 50	5 722 70	<ul style="list-style-type: none"> ○ White - 1 module ● Alu - 1 module ● Magnesium - 1 module
10	0 792 50		
10		5 727 70	

Pack	Cat.Nos		Attenuators
			1 00 V-25 W Allow to adjust power to 25 W from a balanced 100 V loudspeaker line 2 modules
1	Mosaic 0 787 76	Arteor 5 722 84	<ul style="list-style-type: none"> ○ White ● Magnesium
1		5 727 84	

Pack	Cat.Nos		Other audio and video sockets
			Female BNC 75 socket - 1 module Provides the composite video link for any peripheral device such as a DVD drive, camera, video recorder, etc
1	0 787 58	5 722 76	<ul style="list-style-type: none"> ○ White ● Magnesium
1		5 727 76	

