

# Mosaic™ Programme mechanisms

## pushbuttons and accessories



Selection chart for boxes, supports and plates **p. 900-901**

Pack	Cat.Nos.	Pushbuttons 6 A - 250 V~
		Automatic terminals, no tool required
10	0 770 30	<b>One-way pushbuttons</b>
10	0 792 30	○ White - 1 module
10	0 787 14	● Alu - 1 module
		○ White antimicrobial <sup>(1)</sup> - 1 module
10	0 770 40	<b>One-way pushbuttons</b>
10	0 792 40	○ White - 2 modules
10	0 787 15	● Alu - 2 modules
		○ White antimicrobial <sup>(1)</sup> - 2 modules
		<b>Illuminated one-way pushbuttons</b>
		To be equipped with lights (see opposite)
		Supplied with 2 free terminals
10	0 770 33	○ White - 1 module
10	0 770 31	<b>Two-way pushbuttons</b>
		○ White - 1 module
10	0 770 41	○ White - 2 modules
		<b>Illuminated two-way pushbuttons</b>
		To be equipped with lights (see opposite)
10	0 770 32	○ White - 1 module
10	0 792 32	● Alu - 1 module
10	0 770 42	○ White - 2 modules
10	0 792 42	● Alu - 2 modules
10	0 787 16	○ White antimicrobial <sup>(1)</sup> - 2 modules
		<b>Illuminated two-way push-button with free terminal</b>
10	0 770 34	○ White - 1 module
10	0 770 43	<b>Two-way pushbutton with label-holder</b>
		○ White antimicrobial <sup>(1)</sup> - 2 modules

Pack	Cat.Nos.	Accessories
		<b>Locator lights</b>
		For illuminated function of Cat.Nos 0 770 02/12, 0 792 02/12, 0 770 32/42 and 0 792 32/42
10	0 676 86	○ White Connected by direct mounting 230 V. Consumption 0.15 mA
10	0 676 87	12 V - 24 V - 48 V AC and DC consumption: 12 V : 0.4 mA ; 24 V : 1.2 mA ; 48 V : 3.7 mA
		<b>Indicator lights</b>
		For indicator function of two-way switches Cat.Nos 0 770 02/12, 0 792 02/12 and 0 770 33/34
10	0 676 88	Distributed phase wiring monitor light 230 V. Consumption 3 mA
10	0 676 85	Existing wiring monitor light 230 V. Consumption 3 mA
10	0 676 89	12-24-48 V
		<b>Light for socket outlets and 20 AX switches</b>
		For indicator or locator function of Cat.Nos 0 770 62, 0 770 64, 0 770 94
10	0 676 64	230 V Consumption 2.4 mA To be wired
10	0 676 63	<b>Green light for socket outlets</b> 230 V Consumption 2.4 mA To be wired

1: Contains a silver compound to prevent the growth of bacteria on the surface of the plate

Lighting management solutions, **p. 658**



Nurse call units, **p. 909**

