



Technical characteristics **see p. 848 and e-catalogue**

Conform to IEC 61084-2-1 and EN 50085-2-4

For distribution of power vertically

Power supply via the ceiling and/or the floor

To be equipped with Arteor or Mosaic wiring accessories (direct clipping) and Normaclip anti-pullout accessory (p. 845)

Cover width 45 mm

## Pack Cat.Nos 1 compartment - 2 sides columns

Pack	Cat.Nos	1 compartment - 2 sides columns		
		Column body height (m)	Total height between the floor and the ceiling (m)	
			Min.	Max.
1	6 530 10 <sup>1</sup>	2.67	2.77	4.05
	6 530 13 <sup>1</sup>	3.92	4.02	5.30
<b>White finish</b> Aluminium body, PVC covers				
<b>Aluminium finish</b> Aluminium body and covers				
1	6 530 11 <sup>1</sup>	2.67	2.77	4.05
	6 530 14 <sup>1</sup>	3.92	4.02	5.30
<b>Black finish</b> Aluminium body, PVC covers				
1	6 530 12 <sup>1</sup>	2.67	2.77	4.05
	6 530 15 <sup>1</sup>	3.92	4.02	5.30

## Pack Cat.Nos 2 compartments columns

Pack	Cat.Nos	2 compartments columns		
		Column body height (m)	Total height between the floor and the ceiling (m)	
			Min.	Max.
1	6 530 30	2.67	2.77	4.05
	6 530 33	3.92	4.02	5.30
<b>White finish</b> PVC body and covers				
<b>Aluminium finish</b> Aluminium body and covers				
1	6 530 31 <sup>1</sup>	2.67	2.77	4.05
	6 530 34 <sup>1</sup>	3.92	4.02	5.30
<b>Black finish</b> Aluminium body, PVC covers				
1	6 530 32 <sup>1</sup>	2.67	2.77	4.05
	6 530 35 <sup>1</sup>	3.92	4.02	5.30

<sup>1</sup>: For installation with false ceiling, please consult the technical sheet and installation instructions available on e-catalogue

## Pack Cat.Nos 4 compartments columns

Pack	Cat.Nos	4 compartments columns
1	6 530 50	<b>White finish</b> Maximum height 3.30 m Aluminium body, PVC covers
1	6 530 51	<b>Aluminium finish</b> Maximum height 3.30 m Aluminium body and covers
1	6 530 52	<b>Black finish</b> Maximum height 3.30 m Aluminium body, PVC covers

## Pack Cat.Nos 1 compartment 2 sides movable columns

Pack	Cat.Nos	1 compartment 2 sides movable columns
Height 2 m Can be equipped with junction for false ceiling Cat.No 6 530 76		
1	6 530 06	<b>White finish</b> Aluminium body, PVC covers
1	6 530 07	<b>Aluminium finish</b> Aluminium body and covers
1	6 530 08	<b>Black finish</b> Aluminium body, PVC covers

## Pack Cat.Nos 2 compartments movable columns

Pack	Cat.Nos	2 compartments movable columns
Height 2 m Can be equipped with junction for false ceiling Cat.No 6 530 76		
1	6 530 26	<b>White finish</b> Aluminium body, PVC covers
1	6 530 27	<b>Aluminium finish</b> Aluminium body and covers
1	6 530 28	<b>Black finish</b> Aluminium body, PVC covers

## Pack Cat.Nos Junction for false ceiling

1	6 530 76	For movable columns Cat.Nos 6 530 06/07/08/26/27/28
---	----------	--

Technical sheet and installation instructions **see e-catalogue**