


This product is a connected accessory which **requires** you to buy and install the Arteor with Netatmo connected starter pack first.

### Pack contents



Connected socket module

### Safety instructions


This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire.

Before carrying out the installation, read the instructions and take account of the product's specific mounting location.

Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

## Before you start: wiring precautions

To control a **socket**, only use the products:



Connected control socket

Wireless controls for all control points  
(not included in this pack)




**Do not use:** a connected switch (with dimmer option) to control a connected socket module or a traditional power outlet.

## If you are replacing a power outlet controlled by a switch:

### Tip if replacing a switched power outlet:

old flush-mounted switch replaced by the wireless control.

Use a **connector** to connect the two wires.



The circuit must be protected by a 16 A circuit breaker.

## ① Necessary safety precautions

1



**OFF**

Switch OFF the power at the main circuit breaker


2




**Make sure that the power is OFF before continuing with the installation.**

## ② Install the connected socket module

1



## ② Wire the connected socket module



2.5 mm<sup>2</sup> rigid wire recommended

**16 A - 230 V~  
3680 W max  
cos 0.8**

— N (neutral) = blue

— L (live) = any except blue and green/yellow

— ⚬ (earth) = green/yellow

Frequency bands: 2.4 - 2.4835 GHz

Power level: < 100 mW

③ **To add a connected product to your connected installation, you should follow the instructions:**

- in the **user guide in your connected starter pack**
- in the **Legrand Home + Control application (Settings/Add a new product section)**
- or consult the user manual on **legrand.fr**



[www.legrand.fr/reference/574219](http://www.legrand.fr/reference/574219)

LEGRAND - Pro and Consumer Service - BP 30076  
87002 LIMOGES CEDEX FRANCE • [www.legrand.com](http://www.legrand.com)

**SIMPLIFIED EU DECLARATION OF CONFORMITY**

The undersigned,

**Legrand**


declares that the radio-electric equipment referred to in these instructions  
complies with directive 2014/53/EU.

The full text of the EU declaration of conformity  
is available on the following website:

[www.legrandoc.com](http://www.legrandoc.com)

هذا المنتج هو جهاز متصل يتطلب منك أولاً شراء وتركيب علبة المنتجات الأساسية المتصلة ماركة .Arteor with Netatmo

### محتويات العلبة





وحدة المقيس المتصل

### إرشادات الأمان: ⚠

يجب تركيب هذا المنتج طبقاً لقواعد التركيب ويفضل أن يقوم بالتركيب كهربائي مؤهل. فقد يؤدي التركيب الخاطئ و/أو الاستخدام الخاطئ إلى مخاطر التعرض لصدمة كهربائية أو نشوب حريق.  
اقرأ النشرة قبل التركيب، وأفرد مكاناً لتركيب المنتج خاصاً به.  
لا تفتح أو تفك أو تعدل أو تحوّر المنتج ما لم يُشر إلى ذلك بشكل محدد في النشرة. فكل منتجات Legrand يجب فتحها وإصلاحها حصراً من قبل فنيين مدربين ومؤهلين لدى Legrand. وكل فتح أو إصلاح غير مسموح به يُبطل المسؤوليات وحقوق الاستبدال والضمانات. لا تُستخدم سوى إكسسورات من ماركة Legrand حصراً.

قبل بدء العمل: الاحتياطات الخاصة بتوصيلات الأسلاك

للتحكم في المقابس، لا تستخدم سوى المنتجات التالية:



وحدات التحكم اللاسلكية لجميع مواضع التحكم  
(غير موجودة في هذه العلبة)



مقبس التحكم المتصل

يحظر استخدام: المفاتيح المتصلة (مع مفتاح تغيير شدة الإضاءة الاختياري) للتحكم في وحدات المقابس المتصلة أو مأخذ التيار التقليدية.



إذا كنت تنوي استبدال مأخذ تيار يتم التحكم فيه بواسطة مفتاح:

نصيحة في حالة استبدال مأخذ تيار يتم التحكم فيه بواسطة مفتاح:  
استبدال المفتاح القديم المركب داخل الجدار بوحدة التحكم اللاسلكية.



استخدم أداة وصل  
لتوصيل السلكين.

يجب حماية الدائرة الكهربائية  
بقاطع دائرة كهربائية بشدة 16 أمبير.



① احتياطات السلامة الضرورية

2

تأكد من فصل التيار الكهربائي قبل متابعة خطوات عملية التركيب.



1


افصل التيار الكهربائي من القاطع الرئيسي للدائرة الكهربائية





مفصول

② تركيب وحدة المقبس المتصل

1



② قم بتوصيل أسلاك وحدة المقبس المتصل



يوصى باستخدام سلك صلب بمقاس 2.5 ملم<sup>2</sup>

16 أمبير - 230 فولت تقريباً  
3680 واط بحد أقصى  
جتا 0.8

— م (محايد) = أزرق

— ك (خط كهربائي) = أي واحد فيما عدا الأزرق والأخضر/الأصفر

— ⚬ (أرضي) = أخضر/أصفر

نطاقات التردد: 2.4 - 2.4835 جيجاهرتز  
مستوى القدرة: > 100 ملي واط

③ لإضافة منتج متصل إلى المنتجات المتصلة المركبة لديك، يجب اتباع الإرشادات:

- الواردة في دليل المستخدم المرفق مع علبة المنتجات الأساسية المتصلة
- المضمنة في التطبيق **Home + Control** الخاص بشركة **Legrand** (القسم الإعدادات/إضافة منتج جديد)
- أو راجع دليل المستخدم المتوفر على **legrand.fr**



[www.legrand.fr/reference/574219](http://www.legrand.fr/reference/574219)

LEGRAND - Pro and Consumer Service - BP 30076  
87002 LIMOGES CEDEX FRANCE • [www.legrand.com](http://www.legrand.com)

## SIMPLIFIED **EU** DECLARATION OF CONFORMITY

The undersigned,

**Legrand**

declares that the radio-electric equipment referred to in these instructions  
complies with directive 2014/53/EU.

The full text of the EU declaration of conformity  
is available on the following website:

[www.legrandoc.com](http://www.legrandoc.com)