












	Gamme	Référence	Mode	Autotest	Flux lumineux (lm)	Diffuseur	Autonomie	Source lumineuse	IP	CDC	Page catalogue
	B65^{LED}	661426	NP	Non	100	Opale	1h	LED	65	-	1199
		661427	NP	Non	200	Opale	1h	LED	65	-	1199
		661428	NP	Non	350	Opale	1h	LED	65	-	1199
		661429	NP	Non	500	Opale	1h	LED	65	-	1199
		661433	NP - P	Non	200	Opale	1h	LED	65	-	1199
		661434	NP - P	Non	350	Opale	1h	LED	65	-	1199
		661440	NP - P	Non	100	Opale	3h	LED	65	-	1199
	B65^{LED}	660426	NP	Oui	100	Opale	1h	LED	65	-	1199
		660427	NP	Oui	200	Opale	1h	LED	65	-	1199
		660428	NP	Oui	350	Opale	1h	LED	65	CDC400-D04	1199
		660429	NP	Oui	500	Opale	1h	LED	65	CDC400-D04	1199
	B65^{LED} compatible 	662433	NP - P	Oui	250	Opale	1h	LED	65	-	1199
		662434	NP - P	Oui	350	Opale	1h	LED	65	-	1199
662440		NP - P	Oui	100	Opale	3h	LED	65	-	1199	
	B66	661523	NP	Non	250	Transparent	1h	Fluo - 1 x 8W	66	-	1199
	B66 compatible 	662510	NP	Oui	250	Transparent	1h	Fluo - 1 x 8W	66	LB400-D04	1199
		662515	NP	Oui	400	Transparent	1h	Fluo - 1 x 8W	66	LB400-D04	1199
	B66^{LED}	661543	NP - P	Non	250	Transparent	1h	LED	66	-	1199
		661545	NP - P	Non	450	Transparent	1h	LED	66	-	1199
	B66^{LED} compatible 	662542	NP - P	Oui	250	Transparent	1h	LED	66	-	1199
		662544	NP - P	Oui	450	Transparent	1h	LED	66	-	1199
	13W	061847	NP	Non	800	Transparent	1h	Fluo - 1 x 13W	65	-	1200
	ATEX 	662580	NP - P	Oui	400	Transparent	1h	LED	68	-	1200
	BAP à LED⁽¹⁾	661451	NP	Non	900	-	1h	LED	55	-	1201
		661452	NP	Non	1500	-	1h	LED	55	-	1201
		661453	NP	Non	2500	-	1h	LED	55	-	1201
	BAP à LED⁽¹⁾ 	662452	NP	Oui	1500	-	1h	LED	55	-	1201