






## Choix des barres cuivre plates et en C

			≤ 400 A				≤ 800 A		≤ 1000 A		≤ 1600 A			
Supports jeux de barres plates			 réf. 037310		 réf. 037315		 réf. 037320 - 037390		 réf. 037321 - 037391		 réf. 037322/23 - 037392 barres à chant      barres à plat			
Barres cuivre plates			I (A)		I (A)		I (A)		I (A)		I (A)		I (A)	
Réf.	Section (mm)	Nombre de barres par pôle	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30
037434	18 x 4	1	245	200	245	200	245	200	-	-	-	-	-	-
037438	25 x 4	1	280	250	-	-	-	-	-	-	-	-	-	-
037418	25 x 5	1	330	270	330	270	330	270	-	-	-	-	-	-
037419	32 x 5	1	450	400	450	400	450	400	-	-	-	-	-	-
037440	50 x 5	1	-	-	-	-	700	630	700	630	700	630	430	350
		2	-	-	-	-	-	-	-	-	1150	1000	650	510
		3	-	-	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-	-	-
037441	63 x 5	1	-	-	-	-	800	700	800	700	800	700	500	400
		2	-	-	-	-	-	-	-	-	1350	1150	770	590
		3	-	-	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-	-	-
037459	75 x 5	1	-	-	-	-	-	-	950	850	950	850	600	475
		2	-	-	-	-	-	-	-	-	1500	1300	890	700
		3	-	-	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-	-	-
037443	80 x 5	1	-	-	-	-	-	-	1050	900	1000	900	630	500
		2	-	-	-	-	-	-	-	-	1650	1450	940	740
		3	-	-	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-	-	-
037446	100 x 5	1	-	-	-	-	-	-	-	-	1250	1050	750	580
		2	-	-	-	-	-	-	-	-	1900	1600	1120	900
		3	-	-	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-	-	-
	125 x 5	1	-	-	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-	-	-
	80 x 10	1	-	-	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-	-	-
	100 x 10	1	-	-	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-	-	-
	120 x 10	1	-	-	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-	-	-
3		-	-	-	-	-	-	-	-	-	-	-	-	
200 x 10	1	-	-	-	-	-	-	-	-	-	-	-	-	
	2	-	-	-	-	-	-	-	-	-	-	-	-	
	3	-	-	-	-	-	-	-	-	-	-	-	-	



XL-Pro<sup>2</sup> Logiciel  
d'étude de tableaux  
de distribution  
**Voir p. 121** ou  
[www.ecataleg.be](http://www.ecataleg.be)

