




Concevez  
votre **tableau**  
en quelques  
minutes




XL-Pro<sup>2</sup> Logiciel  
d'étude de tableaux  
de distribution  
Voir p. 121 ou  
[www.ecatleg.be](http://www.ecatleg.be)




## PROTECTION DES PERSONNES

### INTERRUPTEURS DIFFÉRENTIELS TX<sup>3</sup> (p. 180)



	In (A)	Bipolaires		Tétrapolaires	
		Réf.	Nb mod.	Réf.	Nb mod.
		Type A			
30 mA	25	411911	2	411931	4
	40	411912	2	411932	4
	63	411913	2	411933	4
100 mA	40	-	-	411937	4
	63	-	-	411938	4
300 mA	40	411922	2	411942	4
	63	411923	2	411943	4
300 mAS	40	411927	2	411947	4
	63	411928	2	411948	4

### DISJONCTEURS DIFFÉRENTIELS DX<sup>3</sup> (p. 195)



Courbe C	In (A)	Phase + neutre		Tétrapolaires	
		Réf.	Nb mod.	Réf.	Nb mod.
		Type A			
10 mA	16	411043	2	-	-
30 mA	16	411061	2	411234	4
	20	411062	2	411235	4
300 mA	16	411083	2	411239	4
	20	411084	2	411240	4




## PROTECTION DES LIGNES

### DISJONCTEURS TX<sup>3</sup> - [3000A] - COURBE C (p. 178)



In (A)	Bipolaires		Tripolaires		Tétrapolaires	
	Réf.	Nb mod.	Réf.	Nb mod.	Réf.	Nb mod.
4	403113	2	403123	3	403133	4
6	403114	2	403124	3	403134	4
10	403115	2	403125	3	403135	4
16	403116	2	403126	3	403136	4
20	403117	2	403127	3	403137	4
25	403118	2	403128	3	403138	4
32	403119	2	403129	3	403139	4
40	403120	2	403130	3	403140	4

### DISJONCTEURS DX<sup>3</sup> - [6000A] - 10kA - COURBE C (p. 182)



In (A)	Bipolaires		Tripolaires		Tétrapolaires	
	Réf.	Nb mod.	Réf.	Nb mod.	Réf.	Nb mod.
1	407792	2	407851	3	407920	4
2	407793	2	407852	3	407921	4
3	407794	2	407853	3	407922	4
4	407795	2	407854	3	407923	4
6	407796	2	407855	3	407924	4
10	407798	2	407857	3	407926	4
16	407800	2	407859	3	407928	4
20	407801	2	407860	3	407929	4
25	407802	2	407861	3	407930	4
32	407803	2	407862	3	407931	4
40	407804	2	407863	3	407932	4
50	407805	2	407864	3	407933	4
63	407806	2	407865	3	407934	4