












	Gamma	Referentie	werkingswijze	Autotest	Lichtstroom (lm)	Verstrooier	Autonomie	Lichtbron	IP	LB	Blz. catalogus
	B65^{LED}	661426	NP	Nee	100	Opaal	1u	LED	65	-	1199
		661427	NP	Nee	200	Opaal	1u	LED	65	-	1199
		661428	NP	Nee	350	Opaal	1u	LED	65	-	1199
		661429	NP	Nee	500	Opaal	1u	LED	65	-	1199
		661433	NP - P	Nee	200	Opaal	1u	LED	65	-	1199
		661434	NP - P	Nee	350	Opaal	1u	LED	65	-	1199
		661440	NP - P	Nee	100	Opaal	3u	LED	65	-	1199
	B65^{LED}	660426	NP	Ja	100	Opaal	1u	LED	65	-	1199
		660427	NP	Ja	200	Opaal	1u	LED	65	-	1199
		660428	NP	Ja	350	Opaal	1u	LED	65	CDC400-D04	1199
		660429	NP	Ja	500	Opaal	1u	LED	65	CDC400-D04	1199
	B65^{LED} compatibel 	662433	NP - P	Ja	250	Opaal	1u	LED	65	-	1199
		662434	NP - P	Ja	350	Opaal	1u	LED	65	-	1199
662440		NP - P	Ja	100	Opaal	3u	LED	65	-	1199	
	B66	661523	NP	Nee	250	Transparant	1u	Fluo - 1 x 8W	66	-	1199
	B66 compatibel 	662510	NP	Ja	250	Transparant	1u	Fluo - 1 x 8W	66	LB400-D04	1199
		662515	NP	Ja	400	Transparant	1u	Fluo - 1 x 8W	66	LB400-D04	1199
	B66^{LED}	661543	NP - P	Nee	250	Transparant	1u	LED	66	-	1199
		661545	NP - P	Nee	450	Transparant	1u	LED	66	-	1199
	B66^{LED} compatibel 	662542	NP - P	Ja	250	Transparant	1u	LED	66	-	1199
		662544	NP - P	Ja	450	Transparant	1u	LED	66	-	1199
	13W	061847	NP	Nee	800	Transparant	1u	Fluo - 1 x 13W	65	-	1200
	ATEX 	662580	NP - P	Ja	400	Transparant	1u	LED	68	-	1200
	BAP met LED	661451	NP	Nee	900	-	1u	LED	55	-	1201
		661452	NP	Nee	1500	-	1u	LED	55	-	1201
		661453	NP	Nee	2500	-	1u	LED	55	-	1201
	BAP met LED 	662452	NP	Ja	1500	-	1u	LED	55	-	1201