




















Keuze van railstelhouders voor Altis vloerverdeelkasten

ALTIS MET DRAAGRAAM VOOR AFDEKPLATEN  (Zie blz. 364)	In max. (A)		Platte koperen staven			
			800	1000	1600	2500
	Montage voor 1 vloerkast	Houders	 037390	 037391	 037392	 037393
 Horizontaal boven	D : 600				● + 047316 + 048026	
	D : 800				● + 047316	● + 047316 + 048027
	D : 1000				● + 047316	● + 047316
 Overdracht horizontaal of horizontaal beneden	D : 600				● + (2x) 048026 + 047316 + 048027 ⁽¹⁾	
	D : 800				● + (2x) 048027 + 047316 ⁽¹⁾	● + (3x) 048027 + 047316 ⁽¹⁾
	D : 1000					● + 048028 + 048027 + 047316 ⁽³⁾
 Verticaal lateraal in mantel	D : 400	●	●	●		
	D : 500	● + 048033 ⁽²⁾	● + 048033 ⁽²⁾	● + 048033 ⁽²⁾		
	D : 600	● + 048033	● + 048033	● + 048033		●
	D : 800/1000	● + 048033	● + 048033	● + 048033		● + 048033
 Verticaal lateraal in vloerkast	D : 800	● + 048033	● + 048033	● + 048033		
	B : 400					
 Verticaal achterwand vloerkast	B : 500	● + 048033		● + 048033		
	B : 600	● + 048033		● + 048033		●
	B : 800	● + 048033		● + 048033		●
	B : 400					
 Horizontaal achterwand vloerkast	B : 500	● + 048027		● + 048027		
	B : 600	● + 048027		● + 048027		● + 048027
	B : 800	● + 048027		● + 048027		● + 048027

(1) Montage enkel met stijprofiel ref. 047480 (2) Gebruik uitsluitend de assemblagekits voor vloerkasten ref. 047681 of 047682 (3) Vloerkast diepte 1000 mm op aanvraag

Keuze van railstelhouders voor standaard Altis vloerkasten

ALTIS ZONDER DRAAGRAAM VOOR AFDEKPLATEN  (Zie blz. 362)	In max. (A)		Platte koperen staven			
			800	1000	1600	4000
	Montage	Houders	 037390	 037391	 037392	 037393
 Horizontaal primair boven of beneden	D : 400				●	
	D : 600				● + 047315	●
	D : 800				● + 047316	●
	D : 1000				● + 047317	● + 047317
 Lateraal verticaal	D : 400	●	●	●		
	D : 600	● + 047315	● + 047315	● + 047315		●
	D : 800	● + 047316	● + 047316	● + 047316		●
	D : 1000	● + 047317	● + 047317	● + 047317		● + 047317
 Verticaal op de achterwand	B : 400	●		●		
	B : 600	● + 047315		● + 047315		
	B : 800	● + 047316		● + 047316		
	B : 1000	● + 047317		● + 047317		