

Keuzetabel Cablofil RVS 304L/RVS 316L

PLAFONDMONTAGE										
Type		Breedte	Draadgoot	Ophangbeugel SF 50	Ophangbeugel SF 100	Wand-/plafondbeugel CSNC	Bevestigingsbeugel CE 40	Ophangklem AS	Montageprofiel RCSN	
CF 54	50 mm	CM000068		CM586144						
		CM000064		CM586144						
	100 mm	CM000078			CM586104	CM556304	CM558058	CM350583	CM013204	
		CM000074			CM586104	CM556304	CM558054	CM350583	CM013204	
	150 mm	CM000088				CM556314		CM350583	CM013304	
		CM000084				CM556314		CM350583	CM013304	
	200 mm	CM000098				CM556324	CM558058	CM350583	CM013304	
		CM000094				CM556324	CM558054	CM350583	CM013304	
	300 mm	CM000108						CM350583	CM013404	
		CM000104						CM350583	CM013404	
	400 mm	CM000208						CM350583	CM013504	
		CM000204						CM350583	CM013504	
	500 mm	CM000308						CM350583	CM013604	
		CM000304						CM350583	CM013604	
	600 mm	CM000408						CM350583		
		CM000404						CM350583		
	CF 30	50 mm	CM000018		CM586144					
			CM000014		CM586144					
100 mm		CM000028			CM586104	CM556304	CM558058	CM350583	CM013204	
		CM000024			CM586104	CM556304	CM558054	CM350583	CM013204	
150 mm		CM000038				CM556314		CM350583	CM013304	
		CM000034				CM556314		CM350583	CM013304	
200 mm		CM000048				CM556324	CM558058	CM350583	CM013304	
		CM000044				CM556324	CM558054	CM350583	CM013304	
300 mm		CM000058						CM350583	CM013404	
		CM000054						CM350583	CM013404	
CF 105	100 mm	CM000898				CM556304		CM350583	CM013204	
		CM000894				CM556304		CM350583	CM013204	
	150 mm	CM000908				CM556314		CM350583	CM013304	
		CM000904				CM556314		CM350583	CM013304	
	200 mm	CM000918				CM556324		CM350583	CM013304	
		CM000914				CM556324		CM350583	CM013304	
	300 mm	CM000928						CM350583	CM013404	
		CM000924						CM350583	CM013404	
	400 mm	CM000938						CM350583	CM013504	
		CM000934						CM350583	CM013504	
	500 mm	CM000948						CM350583	CM013604	
		CM000944						CM350583	CM013604	
	600 mm	CM001038						CM350583		
		CM001034						CM350583		