

Largo

LED



Next generation of outdoor lighting is here. Largo is exceptionally stylish LED-luminaire for tough use. Die-cast aluminium body is a cover for technical superiority like long-lasting LED and changeable lumen output.

DualWhite

Ensto luminaires with DualWhite -solution are equipped with integrated option for light colour temperature switching. You can easily switch between 3000K and 4000K which saves your SKUs and gives you possibility to change colour temperature according to project, with one luminaire.



Dual
White

1 Luminaire,
2 Colour temperatures



"Stylish luminaire
for years to come!"








Structure

- ▶ Body die-cast aluminium
- ▶ Diffuser UV-protected polycarbonate
- ▶ LED-models:
Connected load 9W or 15W, radar models 10.5W and 16.5W, see the luminaire luminous flux from the table
3000 K/4000 K, selected from circuit board switch under diffuser
Ra > 80, power factor 0,9
Ambient temperature - 20 °C - + 30 °C
LED-module lifespan 50 000 h (L70), T_a=25 °C

Mounting

- ▶ To the wall and to the ceiling, -o- 3x2,5 mm²
- ▶ Breakthroughs on luminaires side
- ▶ Cable holes at the bottom of the luminaire and sides also



E number	Type	Product name	Base	Kg	Colour	Luminous flux
Largo LED						
45 032 49	LA270.800BL/DW	LARGO IP66 LED 9W 830/840	LED	1,67	Black	800/400 lm
45 032 52	LA340.1300BL/DW	LARGO IP66 LED 15W 830/840	LED	2,53	Black	1300/850/600 lm
Largo LED with eye-lid						
45 032 55	LA270L.800BL/DW	LARGO L IP66 LED 9W 830/840	LED	1,82	Black	650/330 lm
45 032 58	LA340L.1300BL/DW	LARGO L IP66 LED 15W 830/840	LED	2,77	Black	1000/700/500 lm
Largo LED radar sensor luminaires						
45 032 50	LA270R.800BL/DW	LARGO IP66 LED 10.5W 830/840 R	LED	1,72	Black	800/400 lm
45 032 53	LA340R.1300BL/DW	LARGO IP66 LED 16.5W 830/840 R	LED	2,58	Black	1300/850/600 lm
Largo LED radar sensor luminaires with eye-lid						
45 032 56	LA270LR.800BL/DW	LARGO L IP66 LED 10.5W 830/840 R	LED	1,88	Black	650/330 lm
45 032 59	LA340LR.1300BL/DW	LARGO L IP66 LED 16.5W 830/840 R	LED	2,82	Black	1000/700/500 lm