



door entry kits (continued)

Classe 100 video



Pack	Cat. Nos.	Classe 100X hands free connected video kit with app control and door lock release keyfobs
1	3646 14	<p>Can be easily adapted to a two way system by purchasing an additional internal unit - refer to 2 wire system internal units range, see p. 22-24</p> <p><b>One way hands free kit with :</b></p> <p>Classe 100X16E connected video internal unit :</p> <ul style="list-style-type: none"> <li>• Wi-Fi connectivity. Device can be associated to the Door Entry Classe 100X app (available for Android and iOS) to manage the main video internal unit functions</li> <li>• Inductive loop</li> <li>• 5" LCD display</li> <li>• Wall mounted using bracket (supplied) or table mounted using table support accessories (2 x Cat. No. 3446 92, see p. 25) – to be purchased separately</li> <li>• 2 physical keys for the control of the main functions – answer and end a call – 3 touch keys for the control of the main functions – door lock release, auxiliary relay control and entrance panel activation / scrolling</li> <li>• 4 configurable touch keys that perform different functions – e.g. intercom, additional door lock activation, generic activations</li> <li>• Side lever for adjustment of : colour, brightness and display contrast, audio volume, ringtone volume and Wi-Fi configuration</li> <li>• LED indicators for signalling of call exclusion and Wi-Fi connection</li> </ul> <p>LINEA 3000 push button entrance panel :</p> <ul style="list-style-type: none"> <li>• Zamac front cover</li> <li>• Wide angle colour camera</li> <li>• Proximity reader with a set of 6 coloured keyfobs and 2 clear self adhesive discs. For additional keyfobs, see p. 18</li> <li>• Can manage a maximum of 20 key fobs (125 KHz) for the electric door lock release (including the one for system management)</li> <li>• White LED backlit nameplate</li> <li>• Can be flush or wall mounted, for flush mounting accessories see p. 18 – to be purchased separately</li> <li>• Can be fitted with rainshield (Cat. No. 3430 51, see p. 18) – to be purchased separately</li> <li>• Ingress protection rating of IP 54 and a mechanical protection rating of IK 10</li> </ul>

Pack	Cat. Nos.	Classe 100V hands free video kits
1	3646 12	<p>Can be easily adapted to a two way system by purchasing an additional internal unit - refer to 2 wire system internal units range, see p. 22-24</p> <p><b>One way hands free kit with :</b></p> <p>Classe 100V16E video internal unit :</p> <ul style="list-style-type: none"> <li>• 5" LCD display</li> <li>• Wall mounted using bracket (supplied) or table mounted using table support accessories (2 x Cat. No. 3446 92, see p. 25) – to be purchased separately</li> <li>• 2 physical keys for the control of the main functions – answer and end a call – 3 touch keys for the control of the main functions – door lock release, auxiliary relay control and entrance panel activation /scrolling</li> <li>• 4 configurable touch keys that perform different functions – e.g. intercom, additional door lock activation, generic activations</li> </ul> <p>LINEA 3000 push button entrance panel :</p> <ul style="list-style-type: none"> <li>• Zamac front cover</li> <li>• Wide angle colour camera</li> <li>• White LED backlit nameplate</li> <li>• Can be flush or wall mounted, for flush mounting accessories see p. 18 – to be purchased separately</li> <li>• Can be fitted with rainshield (Cat. No. 3430 51, see p. 18) – to be purchased separately</li> <li>• Ingress protection rating of IP 54 and a mechanical protection rating of IK 10</li> </ul>
1	3646 13	<p><b>One way hands free kit with :</b></p> <p>Classe 100V16B video internal unit :</p> <ul style="list-style-type: none"> <li>• 5" colour LCD display</li> <li>• Side lever for adjustment of : colour, brightness and display contrast, audio and ringtone volume</li> <li>• LED indicator for signalling of call exclusion</li> <li>• Wall mounted using bracket (supplied) or table mounted using table support accessories (2 x Cat. No. 3446 92, see p. 25) – to be purchased separately</li> <li>• 2 physical keys for the control of the main video door entry functions – answer and end a call – and 3 touch keys that allow the door lock release, the entrance panel activation / scrolling and the customisation of a most frequently used quick action – e.g. auxiliary relay control, intercom, additional door lock activation, generic activations</li> </ul> <p>LINEA 2000 push button entrance panel :</p> <ul style="list-style-type: none"> <li>• Aluminium front cover</li> <li>• Colour camera</li> <li>• 1 call push button panel</li> <li>• Green LED backlit nameplate</li> <li>• Ingress protection rating of IP 54 and a mechanical protection rating of IK 07</li> </ul>