



3642 32



3642 31



Pack	Cat. Nos.	Classe 100 hands free audio kit
1	3642 32	<p>Can be easily adapted to a two way system by purchasing an additional internal unit - refer to 2 wire system internal units range, see p. 22 and 24</p> <p><b>One way hands free kit with :</b></p> <p>Classe 100A16E audio internal unit :</p> <ul style="list-style-type: none"> <li>• 2 physical keys for the control of the main door entry functions – answer and end a call – and has 3 touch keys for the control of the main functions – door lock release, auxiliary relay control and entrance panel activation / scrolling</li> <li>• Further 4 configurable touch keys that perform different functions – e.g. intercom, additional door lock activation, generic activations, ringtone volume adjustment (with call exclusion) using the appropriate selector</li> <li>• Wall mounted using bracket (supplied) or table mounted using table support accessory (1 x Cat. No. 3446 92, see p. 25) – to be purchased separately</li> </ul> <p>LINEA 3000 push button entrance panel :</p> <ul style="list-style-type: none"> <li>• Zamac front cover</li> <li>• White LED backlit nameplate</li> <li>• Can be flush or wall mounted, for flush mounting accessories see p. 18 – to be purchased separately</li> <li>• Can be fitted with rainshield (Cat. No. 3430 51, see p. 18) – to be purchased separately</li> <li>• Ingress protection rating of IP 54 and a mechanical protection rating of IK 10</li> </ul>

Pack	Cat. Nos.	Classe 100 audio kit with handset
1	3642 31	<p>Can be easily adapted to a two way system by purchasing an additional internal unit - refer to 2 wire system internal units range, see p. 22 and 24</p> <p><b>One way audio kit with :</b></p> <p>Classe 100A16M audio internal unit :</p> <ul style="list-style-type: none"> <li>• 3 touch keys for the control of the main functions – door lock release, auxiliary relay control and entrance panel activation / scrolling</li> <li>• Further 4 configurable touch keys that perform different functions – e.g. intercom, additional door lock activation, generic activations, ringtone volume adjustment (with call exclusion) using the appropriate selector</li> <li>• Wall mounted using bracket (supplied) or table mounted using table support accessory (1 x Cat. No. 3446 92, see p. 25) – to be purchased separately</li> </ul> <p>LINEA 3000 push button entrance panel :</p> <ul style="list-style-type: none"> <li>• Zamac front cover</li> <li>• White LED backlit nameplate</li> <li>• Can be flush or wall mounted, for flush mounting accessories see p. 18 – to be purchased separately</li> <li>• Can be fitted with rainshield (Cat. No. 3430 51, see p. 18) – to be purchased separately</li> <li>• Ingress protection rating of IP 54 and a mechanical protection rating of IK 10</li> </ul>