




ceiling mounting – RCSN - PFREDF - EDF - R41SP - PFR41S




Dimensions and technical information p. 85, 88-91

NOTE : please use Cat. No. when placing your order


Pack	Cat. Nos.		RCSN – fast fix support rails	
			$\downarrow \uparrow 30 \rightarrow 105 \text{ mm}$ $\curvearrowright 100 \rightarrow 600 \text{ mm}$	
			For trapeze mounting, add 100 mm to width of tray to order correct size support rail - e.g. for 100 mm tray order RCSN200 (Cat. Nos. CM013200 / 03 / 04)	
			For technical information, see p. 85, 88-91	
	GS	GC		L mm
1	CM013150	CM013153	RCSN150	150
1	CM013200	CM013203	RCSN200	200
1	CM013300	CM013303	RCSN300	300
1	CM013400	CM013403	RCSN400	400
1	CM013500	CM013503	RCSN500	500
1	CM013550	CM013553	RCSN550	550
1	CM013600	CM013603	RCSN600	600
1	CM013700	-	RCSN700	700
1	CM013010	CM013013	RCSN1000	1000
1	CM013020	CM013023	RCSN2000	2000
1	CM013030	CM013033	RCSN3000	3000
	304L	316L		
1	-	CM013154	RCSN150	150
1	-	CM013204	RCSN200	200
1	-	CM013304	RCSN300	300
1	-	CM013404	RCSN400	400
1	-	CM013504	RCSN500	500
1	-	-	RCSN550	550
1	-	CM013604	RCSN600	600
1	-	-	RCSN700	700
1	-	CM013014	RCSN1000	1000
1	CM013028	CM013024	RCSN2000	2000
1	CM013038	CM013034	RCSN3000	3000
	EZ+			
1	CM350889		EZ+ colour : black RCSN3000 3000	




Pack	Cat. Nos.		PFREDF – pendant mounting plates	
			$\downarrow \uparrow 30 \rightarrow 105 \text{ mm}$ $\curvearrowright 100 \rightarrow 600 \text{ mm}$	
			For technical information see p. 90	
	GS	GC		daN.m
1	CM561080	-		18
1	304L	316L	CM561084	18




Pack	Cat. Nos.		EDF – profile pendants / mounting rails	
			$\downarrow \uparrow 30 \rightarrow 105 \text{ mm}$ $\curvearrowright 100 \rightarrow 600 \text{ mm}$	
			For technical information see p. 89-90	
	GS	GC		L mm
1	CM561010	CM561013	EDF2000	2000
1	304L	316L	EDF2000	2000



Pack	Cat. Nos.		R41SP – pendants / mounting rails (heavy duty)	
			$\downarrow \uparrow 30 \rightarrow 150 \text{ mm}$ $\curvearrowright 100 \rightarrow 600 \text{ mm}$	
			For technical information, see p. 91	
	GS	EZ+		L mm
1	CM343930	CM343932	R41SP3000	3000



Pack	Cat. Nos.		PFR41S – pendant mounting plate (heavy duty)	
			$\downarrow \uparrow 30 \rightarrow 105 \text{ mm}$ $\curvearrowright 100 \rightarrow 600 \text{ mm}$	
			For technical information see p. 91	
	GS			daN
1	CM595380			45



Key: GS Pre-galvanised	304L Stainless steel 304 L
EZ+ Additional coating after electrogalvanisation (black)	316L Stainless steel 316 L
GC Hot dip galvanised after manufacture	

For detailed information related to finishes, refer to p. 132-133

All dimensions (mm) are nominal