3-pole contactors CTX³

130 A to 800 A industrial contactors

4 162 46

4 162 56

4 162 96

4 163 56

Technical characteristics **p. 288**
Dimensions **p. 290 to 295**

Conform to IEC 60947-1, IEC 60947-4-1
Can be equipped with RTX³ thermal relays (p. 284) add-on auxiliary contact blocks, time delay blocks (except CTX³ 225/400/800) and CTX³ interlocking (p. 286)

CTX³ 150

With integrated auxiliary contacts

Pack	Cat.Nos		3-phase motor 400/415 V	Control Voltage	Integrated auxiliary contacts
	Screw terminals	Cage terminals			
			130 A (AC3) - 160 A (AC1)		
1	4 162 40	4 162 50	60 kW	24 V~	2 NO + 2 NC
1	4 162 41	4 162 51	60 kW	24 V⎓	2 NO + 2 NC
1	4 162 46	4 162 56	60 kW	100-240 V~/⎓	2 NO + 2 NC
1	4 162 49	4 162 59	60 kW	400-440 V~	2 NO + 2 NC
			150 A (AC3) - 210 A (AC1)		
1	4 162 60	4 162 70	75 kW	24 V~	2 NO + 2 NC
1	4 162 61	4 162 71	75 kW	24 V⎓	2 NO + 2 NC
1	4 162 66	4 162 76	75 kW	100-240 V~/⎓	2 NO + 2 NC
1	4 162 69	4 162 79	75 kW	400-440 V~	2 NO + 2 NC

CTX³ 225

With integrated auxiliary contacts

Pack	Cat.Nos	3-phase motor 400/415 V	Control Voltage	Integrated auxiliary contacts
	Screw terminals			
		185 A (AC3) - 230 A (AC1)		
1	4 162 80	90 kW	24 V~/⎓	2 NO + 2 NC
1	4 162 86	90 kW	100-240 V~/⎓	2 NO + 2 NC
1	4 162 89	90 kW	380-450 V~	2 NO + 2 NC
		225 A (AC3) - 275 A (AC1)		
1	4 162 90	132 kW	24 V~/⎓	2 NO + 2 NC
1	4 162 96	132 kW	100-240 V~/⎓	2 NO + 2 NC
1	4 162 99	132 kW	380-450 V~	2 NO + 2 NC

CTX³ 400

With integrated auxiliary contacts

Pack	Cat.Nos	3-phase motor 400/415 V	Control Voltage	Integrated auxiliary contacts
	Screw terminals			
		265 A (AC3) - 300 A (AC1)		
1	4 163 06	147 kW	100-240 V~/⎓	2 NO + 2 NC
1	4 163 09	147 kW	380-450 V~	2 NO + 2 NC
		330 A (AC3) - 350 A (AC1)		
1	4 163 16	160 kW	100-240 V~/⎓	2 NO + 2 NC
1	4 163 19	160 kW	380-450 V~	2 NO + 2 NC
		400 A (AC3) - 450 A (AC1)		
1	4 163 26	200 kW	100-240 V~/⎓	2 NO + 2 NC
1	4 163 29	200 kW	380-450 V~	2 NO + 2 NC

CTX³ 800

With integrated auxiliary contacts

Pack	Cat.Nos	3-phase motor 400/415 V	Control Voltage	Integrated auxiliary contacts
	Screw terminals			
		500 A (AC3) - 580 A (AC1)		
1	4 163 36	265 kW	200-240 V~/⎓	2 NO + 2 NC
1	4 163 39	265 kW	380-450 V~	2 NO + 2 NC
		630 A (AC3) - 660 A (AC1)		
1	4 163 46	330 kW	200-240 V~/⎓	2 NO + 2 NC
1	4 163 49	330 kW	380-450 V~	2 NO + 2 NC
		800 A (AC3) - 900 A (AC1)		
1	4 163 56	440 kW	200-240 V~/⎓	2 NO + 2 NC
1	4 163 59	440 kW	380-450 V~	2 NO + 2 NC

Add-on auxiliary contact blocks
p. 286

Other control voltage, spare coils for CTX³ 3-pole contactors, **please, consult us**