

DPX³ 630

equipment and accessories (continued)



4 226 30



0 261 40



0 262 50



0 262 48

Pack	Cat.Nos	Rotary handles
1	0 262 41	Direct on DPX³
1	4 222 38	Standard (grey) For emergency use (red/yellow) - can be fitted on Cat.Nos 0 262 22, 0 262 41 or 0 262 81
		Vari-depth handle IP 55
		Comprising: connection rod, bracket, self-adhesive drilling template, mounting accessories and door lock mechanism
1	0 262 81	Standard (grey)
1	0 262 82	For emergency use (red/yellow) can be fitted on Cat.Nos 0 262 81 or 0 262 41
		Locking accessories
1	4 228 07	Mechanical support for locking vari-depth handle To be equipped with universal key-locks Cat.Nos 4 238 80/81/82/83 (p. 180)
		Motor-driven handles
		Front installation
1	4 226 30	230 V~
		Front installation - fast closing
1	0 261 40	24 V~/=
1	0 261 41	48 V~/=
1	0 261 44	230 V~
		Accessories
1	4 228 06	Mechanical support for locking motor-driven handle To be equipped with universal key-locks Cat.Nos 4 238 80/81/82/83 (p. 180)
		Universal key locks for DPX³ 125/160/250 HP and DPX³ 630/1600
		Allow locking of rotary handles, draw-out mechanisms or motor-driven handles To be used in combination with locking accessories Cat.Nos 4 228 06/07/08/09/10 (p. 179, 180 and 183) and 4 238 04/05/45/46/62/63 (p. 169 and 174)
1	4 238 80	Key barrel and flat key with random mapping
1	4 238 81	Key barrel and flat key with fixed mapping EL43525
1	4 238 82	Key barrel and flat key with fixed mapping EL43363
1	4 238 83	Key barrel and star key with random mapping

Pack	Cat.Nos	Accessories
1	0 262 30	Insulated shields (phase barriers) Set of 3
1	0 262 44 0 262 45	Sealable terminal shields Set of 2
		Padlock
1	0 262 40	For locking in "OPEN" position
		Cage terminals
1	0 262 50	Set of 4 terminals for cable 300 mm ² max. (rigid) or 240 mm ² max. (flexible)
1	0 262 51	Set of 4 high-capacity terminals for cable 2 x 240 mm ² (rigid) or 2 x 185 mm ² (flexible)
		Adaptor for lug
1	0 262 46	For connecting bare cables with wide lugs Set of 4 adaptors + insulated shields
		Extended front terminals
1	0 262 47	Set of 4
		Spreaders
1	0 262 48 0 262 49	Set of incoming or outgoing spreaders
		Rear terminals
		Used to convert the fixed version with front terminals to the fixed version with rear terminals
1	0 263 52 0 263 53	Set of incoming or outgoing flat terminals
		IP 20 terminal covers
1	4 222 34 4 222 35	Set of 2 terminal covers