


Equipment for XL³ 4000 - for mounting on adjustable plate: DPX³ 160, DPX³ 250 fixed version

Equipment for XL³ 4000

for mounting on adjustable plate: plug-in DPX³ 160, DPX³ 250



0 209 10



0 208 13



0 212 11



0 212 13

Selection chart p. 376 to 379

Selection chart p. 376 to 379

Pack	Cat.Nos	Fixing fixed version DPX ³ 160/250 with front or rear terminals
		Adjustable fixing devices for MCCBs in vertical position The MCCBs are fixed using special mounting plates Allow mounting direct rotary handles and front motor-driven handles
1	24 modules 36 modules 0 207 90 0 207 61	For 1 to 3 DPX ³ For 2 DPX ³ in transfer switch
1	0 206 63	
		Mounting plates for devices in vertical position
1	0 207 49	For 1 DPX ³ 160
1	0 206 71	For 1 DPX ³ 160 in transfer switch
1	0 207 64	For 1 DPX ³ 250
1	0 206 73	For 1 DPX ³ 250 in transfer switch
		Adjustable plates for devices in horizontal position
1	24 modules 0 207 94	For 1 DPX ³ 160
1	0 207 96	For 1 DPX ³ 250
		Metal faceplates for devices in vertical position
		For DPX³ with or without motor driven handle 1/4 turn With captive screws
1	24 modules 36 modules 0 208 10 ¹ 0 209 60 ²	
1	0 209 10 ² 0 209 60 ²	
1	0 208 05 ¹	For 1 to 3 DPX³ with direct rotary handle 1/4 turn With captive screws
1	0 209 05 ² 0 209 65 ²	
		Metal faceplates for devices in horizontal position
		Allow mounting front motor-driven handles
1	24 modules 0 208 13 ²	For 1 DPX³ 160 1/4 turn With captive screws
1	0 209 13 ¹	
1	0 208 17 ²	For 1 DPX³ 250 1/4 turn With captive screws
1	0 209 17 ¹	

1: Hinges Cat.No 0 209 59 (p. 394) available as an option
2: For fastening and sealing

Pack	Cat.Nos	Fixing plug-in version DPX ³ 160/250 with front or rear terminals
		Adjustable fixing devices in vertical position The devices are fixed using special mounting plates Allow mounting direct rotary handles and front motor-driven handles
1	0 207 91	For 1 to 3 DPX ³
1	0 206 69	For 2 DPX ³ in transfer switch
		Mounting plates for devices in vertical position
1	0 207 59	For 1 DPX ³ 160
1	0 206 81	For 1 DPX ³ 160 in transfer switch
1	0 207 69	For 1 DPX ³ 250
1	0 206 83	For 1 DPX ³ 250 in transfer switch
		Adjustable plates for devices in horizontal position
1	0 207 95	For 1 DPX ³ 160
1	0 207 97	For 1 DPX ³ 250
		Metal faceplates for devices in vertical position
		For 1 to 3 DPX³ with or without front motor-driven handle With hinges and lock
1	0 212 11	
		For 1 to 3 DPX³ with direct rotary handle With hinges and lock
1	0 212 08	
		Metal faceplate for devices in horizontal position
		Allow mounting front motor-driven handles
1	0 212 13	For 1 DPX³ With hinges and lock