

Solid faceplates for XL³ 4000




0 208 44



0 209 59

Pack	Cat.Nos	Metal solid faceplates
		1/4 turn For fastening and sealing
	24 modules	Height (mm)
1	0 208 40	50
1	0 208 41	100
1	0 208 42	150
1	0 208 43	200
1	0 208 44	300
1	0 208 45	400
1	0 208 46	600
		With captive screws Hinges Cat.No 0 209 59 available as an option
	24 modules 36 modules	Height (mm)
1	0 209 40 0 209 90	50
1	0 209 41 0 209 91	100
1	0 209 42 0 209 92	150
1	0 209 43 0 209 93	200
1	0 209 44 0 209 94	300
1	0 209 45 0 209 95	400
1	0 209 46 0 209 96	600
		Accessories for natural ventilation
		Assist natural ventilation Screw mounting
	24 modules	Perforated faceplates Height 200 mm
1	0 209 49	
		Perforated panels For plinth 725 mm width
1	0 205 44	
		Distance piece Distance piece for roof heightening
1	0 205 46	
		Accessories for faceplates
		Hinges Set of 2 Fit on screw mounting faceplates
1	0 209 59	
		Blanking plates For metal or insulated faceplates 18 modules, can be separated into modules or 1/2 modules
10	0 016 65	
		Clip-on holder for adhesive labels Supplied with sheet of labels for marking rows on faceplate
10	3 397 55	24 modules

Universal plates for XL³ 4000



0 206 42



0 206 02

Pack	Cat.Nos	Universal plates
		Fit onto the functional uprights
		Perforated plates width 600 mm
1	0 206 41	Height 200 mm
1	0 206 42	Height 400 mm
		Solid plates width 600 mm
1	0 206 43	Height 200 mm
1	0 206 44	Height 400 mm
1	0 206 45	Height 600 mm
		Solid plates width 850 mm
1	0 206 46	Height 400 mm
		Adjustable solid plates
1	0 206 40	Height 100 mm, width 600 mm
1	0 206 47	Height 200 mm, width 600 mm
1	0 206 48	Height 400 mm, width 600 mm
1	0 206 49	Height 200 mm, width 850 mm
1	0 206 90	Height 100 mm, width 850 mm
		Protection seal
1	0 202 40	For cut-out protection on plate Length 10 m, can be cut to length
		Solid mounting plate
1	0 205 40	Supplied with depth adjustment runner Height 1800 mm, width 600 mm
		Universal  rails
		Fit onto the functional uprights
1	0 206 04	Width 600 mm (24 modules)
1	0 206 54	Width 850 mm (36 modules)
		Adjustable universal fixing devices
		Comprising a  rail and 2 adjustable fixing brackets
		Fit onto the functional uprights
1	0 206 02	For 24 modules cabinets and enclosures
1	0 206 52	For 36 modules cabinets and enclosures