



Isolating supports for busbars for XL³ enclosures



0 373 10



0 373 24



Dimensions and distances between the supports **p. 406 to 410**

"Standard" distribution

Pack	Cat.Nos	1 bar per pole universal supports	
10	0 373 98	≤ 280 A Single pole support for flat copper bars 12 x 2 or 14 x 4 mm	
10	0 374 37	Single pole support for flat copper bars 15 x 4, 18 x 4 or 25 x 4 mm	
5	0 373 96	Set of 2 four pole supports for flat copper bars 12 x 2 or 12 x 4 mm	
1	0 374 32	Set of 2 four pole supports for flat copper bars 15 x 4 or 18 x 4 mm	
1	0 374 36	Set of 2 four pole supports for flat copper bars 25 x 4 mm	
1 bar per pole			
		≤ 400 A	
1	0 373 15	Support for flat copper bars 18 x 4, 25 x 5 and 32 x 5 mm For XL ³ 400 cabinets and enclosures	
1	0 373 10	Support for flat copper bars 18 x 4, 25 x 4, 25 x 5 and 32 x 5 mm, in sloping position to create a vertical busbars at back For direct mounting on solid or perforated plate	
		≤ 800 A	
1	0 373 20	Support for flat copper bars 18 x 4, 25 x 5, 32 x 5, 50 x 5 and 63 x 5 mm in sloping position	
		≤ 1000 A	
1	0 373 21	Support for flat copper bars 50 x 5, 63 x 5, 75 x 5 and 80 x 5 mm in staggered position	

Pack	Cat.Nos	1 or 2 bars per pole
		Supports for flat copper bars 50 x 5, 63 x 5, 75 x 5, 80 x 5 and 100 x 5 mm, in aligned position
		≤ 1600 A
1	0 373 22	Fixed support
1	0 373 23	Additional support Mounted in addition to fixed support Cat.No 0 373 22 to comply with the distances (Isc withstand)
		1 to 4 bars per pole
		≤ 4000 A
		Supports for 4 flat bars from 50 x 5 to 125 x 5 mm or 3 bars from 50 x 10 to 120 x 10 mm, in aligned position
1	0 373 24	Fixed support
1	0 373 25	Additional support Mounted in addition to fixed support Cat.No 0 373 24 to comply with the distances (Isc withstand)
		≤ 6300 A
		Reinforced 4P isolating supports Hold flat copper bars in position Up to three 200 x 10 mm bars per pole
1	0 373 12	Fixed support
1	0 373 13	Additional support Mounted in addition to fixed support Cat.No 0 373 12 to comply with the distances (Isc withstand)
		Fixing supports
		Adjustable crosspieces
1	0 205 51	Set of 2 crosspieces length 350 mm
1	0 205 52	Set of 2 crosspieces length 600 mm
1	0 205 53	Set of 2 crosspieces length 850 mm
		Crosspieces for partial chassis
1	0 205 31	Set of 2 fixed crosspieces length 350 mm
1	0 205 32	Set of 2 fixed crosspieces length 600 mm
		Extension piece
1	0 373 14	For mounting busbars supports Cat.No 0 373 15 in XL ³ 800 and 4000 cabinets and enclosures



Optimised and increased safety
distribution systems,
see Product Guide

