



Technical characteristics p. 287 to 289

**CTX<sup>3</sup> add-on auxiliary contact blocks**

Pack	Cat.Nos	CTX <sup>3</sup> add-on auxiliary contact blocks
		<b>Front mounting</b> For CTX <sup>3</sup> 3P from 9 A to 150 A (AC-3) and CTX <sup>3</sup> 4P from 40 A to 135 A (AC-1) 2 and 4-pole lth: 16 A
20	4 168 50	1 NO + 1 NC
20	4 168 51	2 NO
20	4 168 52	2 NC
10	4 168 53	4 NO
10	4 168 54	3 NO + 1 NC
10	4 168 55	2 NO + 2 NC
10	4 168 56	1 NO + 3 NC
10	4 168 57	4 NC
		<b>Side mounting</b> 2-pole Mounting on both sides
1	4 168 58	For CTX <sup>3</sup> 3P from 9 A to 150 A (AC-3) 1 NO + 1 NC - lth: 16 A
1	4 168 59	For CTX <sup>3</sup> 3P from 185 A to 800 A (AC-3) and CTX <sup>3</sup> 4P from 165 A to 900 A (AC-1) 1 NO + 1 NC - lth: 16 A
1	4 168 49	For CTX <sup>3</sup> 4P from 40 A to 135 A (AC-1) 1 NO + 1 NC - lth: 16 A

Pack	Cat.Nos	CTX <sup>3</sup> time delay blocks
		For CTX <sup>3</sup> 3P form 9 A to 150 A (AC-3) Time delay: 1 to 30 s Front mounting
1	4 168 70	24-48 V~/=
1	4 168 71	110-230 V~
		<b>On delay</b>
1	4 168 72	24-48 V~/=
1	4 168 73	110-230 V~

Pack	Cat.Nos	CTX <sup>3</sup> capacitor switching units
		AC-6b Operating power from 9.7 kVAR to 62 kVAR (400/440 V)
1	4 168 74	For contactors CTX <sup>3</sup> 3P from 9 to 40 A
1	4 168 75	For contactors CTX <sup>3</sup> 3P 50 and 65 A with screw terminals
1	4 168 76	For contactors CTX <sup>3</sup> 3P 50 to 100 A with cage terminals
1	4 168 77	For contactors CTX <sup>3</sup> 3P 75 to 100 A with screw terminals

**CTX<sup>3</sup> interlocking**

Pack	Cat.Nos	CTX <sup>3</sup> interlocking
		Component parts for assembling by customer Horizontal mounting
		<b>Interlock units</b>
1	4 168 79	Mechanical interlocks for CTX <sup>3</sup> 4P from 40 to 135 A (AC-1) (p. 285)
1	4 168 80	Mechanical interlocks for CTX <sup>3</sup> 3P from 9 to 150 A (p. 282-283)
1	4 168 87	Provides 2 NC contacts for use in electrical interlocking Mechanical interlocks for CTX <sup>3</sup> 3P from 185 to 400 A and CTX <sup>3</sup> 4P from 165 to 500 A (p. 285)
1	4 168 88	Mechanical interlocks for CTX <sup>3</sup> 3P from 500 to 800 A (p. 283)
1	4 168 89	Mechanical interlocks for CTX <sup>3</sup> 4P from 750 to 900 A (p. 285)
		<b>Wire kits</b> Used for making reversing between two 3P contactors (varistors)
4	4 168 82	For CTX <sup>3</sup> 22
6	4 168 83	For CTX <sup>3</sup> 40
2	4 168 84	For CTX <sup>3</sup> 65
1	4 168 85	For CTX <sup>3</sup> 100

Pack	Cat.Nos	Boxes for motor starter
1	4 168 90	For CTX <sup>3</sup> 22 equipped with RTX <sup>3</sup> 40 (0.1 - 22 A) Without pushbuttons
1	4 168 91	With pushbuttons

Pack	Cat.Nos	CTX <sup>3</sup> transient voltage suppressor blocks
		Absorbs the surge arisen out of the coil of the contactor (varistors)
10	4 168 95	24-48 V~/=
10	4 168 96	100-125 V~/=
10	4 168 97	200-240 V~/=
10	4 168 98	380-400 V~

Pack	Cat.Nos	CTX <sup>3</sup> terminals covers
1	4 168 42	For CTX <sup>3</sup> 3P from 185 to 225 A (AC-3)
1	4 168 43	For CTX <sup>3</sup> 3P from 265 to 400 A (AC-3)
1	4 168 44	For CTX <sup>3</sup> 3P from 500 to 800 A (AC-3)
1	4 168 45	For CTX <sup>3</sup> 4P from 165 to 330 A (AC-1)
1	4 168 46	For CTX <sup>3</sup> 4P from 420 to 500 A (AC-1)
1	4 168 47	For CTX <sup>3</sup> 4P from 750 to 900 A (AC-1)

Pack	Cat.Nos	CTX <sup>3</sup> safety front cover
150	4 168 40	For CTX <sup>3</sup> 3P from 9 to 150 A (AC-3) and CTX <sup>3</sup> 4P from 40 to 135 A (AC-1)
150	4 168 41	For CTX <sup>3</sup> 3P from 85 to 800 A (AC-3) and CTX <sup>3</sup> 4P from 165 to 900 A (AC-1)

