

Distribution terminal blocks




0 048 03



0 048 22



0 048 15



0 048 32

Pack	Cat.Nos	Distribution terminal blocks	
		Conform to standard IEC 60998-2-1 Supplied ready for use (screws not tightened) 100 A max. - 400 V \sim with 25 mm ² input 80 A max. - 400 V \sim with 16 mm ² input Icc = 10 kA rms	
		Screw terminal blocks	
		Fit with \varnothing D4 screws	
		Number of connections (mm ²)	Length (mm)
10	0 048 01	1 x 6 to 25 + 4 x 1.5 to 16	45
10	0 048 03	1 x 6 to 25 + 8 x 1.5 to 16	73
10	0 048 05	1 x 6 to 25 + 14 x 1.5 to 16	122
10	0 048 06	1 x 6 to 25 + 19 x 1.5 to 16	157
10	0 048 07	1 x 6 to 25 + 25 x 1.5 to 16	192
		Terminal blocks on support	
		Mounting on or rail with universal support Cat.No 0 048 11, or on 12 x 2 flat bar	
		Supplied with Duplix markers	
10	0 048 20 ¹	4 x 1.5 to 16	47
10	0 048 22 ¹	8 x 1.5 to 16	75
10	0 048 24 ¹	1 x 6 to 25 + 12 x 1.5 to 16	113
10	0 048 25 ¹	1 x 6 to 25 + 16 x 1.5 to 16	141
10	0 048 26 ¹	1 x 6 to 25 + 21 x 1.5 to 16	176
10	0 048 28 ¹	1 x 6 to 25 + 33 x 1.5 to 16	276
		IP 2X terminal blocks	
		Mounting on or rail with universal support Cat.No 0 048 11, or on 12 x 2 flat bar	
10	0 048 16	0 048 15	1 x 10 to 35 + 5 x 6 to 25
10	0 048 50	0 048 40	4 x 1.5 to 16
10	0 048 52	0 048 42	8 x 1.5 to 16
10	0 048 54	0 048 44	1 x 6 to 25 + 12 x 1.5 to 16
10		0 048 45	1 x 6 to 25 + 16 x 1.5 to 16
10		0 048 46	1 x 6 to 25 + 21 x 1.5 to 16
10		0 048 48	2 x 6 to 25 + 33 x 1.5 to 16
		Earth (green)	
10	0 048 30		4 x 1.5 to 16
10	0 048 32		8 x 1.5 to 16
10	0 048 34		1 x 6 to 25 + 12 x 1.5 to 16
10	0 048 35		1 x 6 to 25 + 16 x 1.5 to 16
10	0 048 36		1 x 6 to 25 + 21 x 1.5 to 16
10	0 048 38		2 x 6 to 25 + 33 x 1.5 to 16

Supports for terminal blocks

1	0 048 10	Distribution block support for connecting up to 4 IP 2X terminal blocks or terminal blocks on support of the same size, to create a distribution block
5	0 048 11	Universal support for mounting an terminal blocks on or rail
5	0 048 17	35-holes empty support, for screw terminal blocks Length: 276 mm

Flat bar 12 x 2

10	0 048 19	Length: 1 meter
----	----------	-----------------

1: Each terminal block is supplied with:
- 2 green Duplix marked \pm - 2 blue Duplix marked N
- 2 red Duplix marked L

Supply busbars and distribution terminal blocks

Selection of protections for supply busbars (p. 297)

Supply busbars Cat.Nos	Protections Cat.Nos
4 049 26/28/33/37	4 049 89
4 049 10/34/42/43	4 049 90
4 049 15/16/19/20/40/41/44/45/66/67	4 049 91
4 049 09/11/12	4 049 93
4 049 13/14/38/39	4 049 94
4 049 17/18/87	4 049 95

Mounting of terminal blocks on support


On 12 x 2 flat bar



On support for terminal blocks Cat.No 0 048 17


Enables you to make exactly the right number of connections

- Example:



Universal support Cat.No 0 048 11

Mounted on or rail, takes all terminal blocks



On distribution block support Cat.No 0 048 10

Possibility of forming a 2P, 3P or 4P distribution block by associating IP 2X terminal blocks

