

CAB 3™ marking system

accessories



Pack	Cat.Nos	CAB 3 accessories	
		Marker-holders For cables cross-section from 10 mm ² to 70 mm ² Capacity: 8 digits, letters or symbols markers from 0.5 to 1.5 mm ² or 1.5 to 2.5 mm ² cross section Black	
100	0 384 90	10 to 16 mm ² cross-section	
50	0 384 91	25 to 35 mm ² cross-section	
50	0 384 92	50 to 70 mm ² cross-section	
		Support for markers Can be clipped on Viking 3 terminal blocks with screw connection Capacity: 7 markers from 0.15 to 0.5 mm ² 6 markers from 0.5 to 1.5 mm ²	
100	0 383 92		
		Transparent applicators For rapid selection and application of markers onto cable (except Cat.No 0 381 50 to 0 381 55 and Cat.No 0 381 60 to 0 381 65)	
		For markers cross-section (mm ²)	Applicator colour for identification of cross-section
10	0 383 94	0.15 to 0.5	green
10	0 383 95	0.5 to 1.5	red
10	0 383 96	1.5 to 2.5	blue
10	0 383 97	4 to 6	yellow
		On-site toolbox With removable tray for CAB 3 markers and applicators, Starfix ferrules... Height 85 mm, depth 280 mm, width 450 mm Metal, padlockable Supplied empty	
1	0 382 00		


CAB 3™ marking system

for wiring and Viking 3 terminal blocks

Dimensions

Markers

Polyamide 6/6



Dimensions	Cable cross-section (mm ²)			
	0.15 to 0.5	0.5 to 1.5	1.5 to 2.5	4 to 6
A (mm)	5	5	5.6	8
B (mm)	5.05	6.4	7.6	9.6
C (mm)	3.7	4.3	4.9	7.1
D (mm)	2.3	3	3	3
Ø mini/maxi (mm)	0.8/2.2	2.2/3	2.8/3.8	4.3/5.3


Cat.Nos 0 381 50 to 0 381 55 et 0 381 60 to 0 381 65: no liking stud.
D = 6 mm

Marker holders

Cat.No 0 384 90


Cat.No 0 384 91

Cat.No 0 384 92




Dim.	Section of cable for marking (mm ²)		
	10 to 16	25 to 35	50 to 70
B (mm)	18	24.3	27.2
C (mm)	8.9	12.2	17.2
D (mm)	7	7	10

Support for markers Cat.No 0 383 92



Characteristics and dimensions of on-site toolbox

Cat.No 0 382 00




- Bottom tray consists of:
- 8 medium slots (around 8 CAB 3 boxes)
 - 1 large slot
- Top tray consists of:
- 12 small slots (<=> approx. 6 boxes of CAB 3)
 - 1 medium slot for applicators
- Capacity: approx. 15000 CAB 3 markers

Examples

On terminal blocks with support Cat.No 0 383 92



On power terminal blocks



On cable with marker-holder Cat.No 0 384 92

