

XL³ S 630

equipment for mounting DRX/DPX³ 250 HP on a plate



XL³ S 630

equipment for mounting DPX-IS 250 on a plate



3 386 03



3 386 01



3 389 20



3 382 73



3 386 56

Selection chart p. 326 to 331

Reduced height fixing plates for DRX/DPX³ 250 HP - horizontal mounting

Pack	Cat.Nos	
	3P	
1	3 386 00	For 16-module enclosure
1	3 386 03	For 24-module enclosure
1	3 386 06	For 36-module enclosure

Fixing plates for DRX/DPX³ 250 HP - horizontal mounting

Pack	Cat.Nos	
	3P/4P	
1	3 386 01	For 16-module enclosure
1	3 386 04	For 24-module enclosure
1	3 386 07	For 36-module enclosure

Fixing plates for DRX/DPX³ 250 HP - vertical mounting


Pack	Cat.Nos	
	3P	
1	3 386 20	For 16-module enclosure
1	3 386 23	For 24-module enclosure
1	3 386 26	For 36-module enclosure

DRX/DPX³ 250 HP with or without e.l.c.b

Pack	Cat.Nos	
	4P	
1	3 386 21	For 16-module enclosure
1	3 386 24	For 24-module enclosure
1	3 386 27	For 36-module enclosure


Reduced height faceplates for DPX³ 250 HP - horizontal mounting

Pack	Cat.Nos	
	3P	Fixed with 1/4 turn screws or screws Height: 150 mm
1	3 386 50	For 16-module enclosure
1	3 386 53	For 24-module enclosure
1	3 386 56	For 36-module enclosure




Faceplates for DPX³ 250 HP - horizontal mounting

Pack	Cat.Nos	
	4P	Fixed with 1/4 turn screws or screws For DPX ³ 250 HP with or without e.l.c.b Height: 200 mm
1	3 386 51	For 16-module enclosure
1	3 386 54	For 24-module enclosure
1	3 386 57	For 36-module enclosure



Faceplates for DPX³ 250 HP - vertical mounting

Pack	Cat.Nos	
	3P/4P	Fixed with 1/4 turn screws or screws DPX ³ 250 HP with or without e.l.c.b Height: 300 mm
1	3 386 71	For 16-module enclosure
1	3 386 74	For 24-module enclosure
1	3 386 77	For 36-module enclosure



Selection chart p. 326 to 331

Fixing plates for DPX-IS 250 - horizontal mounting


Pack	Cat.Nos	
	3P/4P	
1	3 389 02	For 24-module enclosure
1	3 389 04	For 36-module enclosure

Fixing plates for DPX-IS 250 - vertical mounting

Pack	Cat.Nos	
	3P/4P	
1	3 389 20	For 16-module enclosure
1	3 389 22	For 24-module enclosure
1	3 389 24	For 36-module enclosure


Faceplates for DPX-IS 250 - horizontal mounting

Pack	Cat.Nos	
	3P/4P	Fixed with 1/4 turn screws or screws Height: 300 mm
1	3 389 42	For 24-module enclosure
1	3 389 44	For 36-module enclosure



Faceplates for DPX-IS 250 - vertical mounting

Pack	Cat.Nos	
	3P/4P	Fixed with 1/4 turn screws or screws Height 300 mm
1	3 382 71	For 16-module enclosure
1	3 382 72	For 24-module enclosure
1	3 382 73	For 36-module enclosure



Faceplates for DRX 250 HP p. 336