

Arteor™ load selection charts

Load selection charts

	Cat.Nos	Type of cabling	Universal					
			LEDs and CFLs		Halogen/Incandescent lamps		LEDs, CFLs, halogen, fluorescent tube with ferromagnetic or electronic transformer	
			110 V~	240 V~	110 V~	240 V~	110 V~	240 V~
Contactless switch for lighting	5 743 34	With Neutral	100 VA	200 VA	100 W	200 W	100 VA	200 VA
		Without Neutral	5 - 100 VA	5 - 200 VA	5 - 100 W	5 - 200 W	5 - 100 VA	5 - 200 VA
	5 743 37	With Neutral	100 VA	200 VA	100 W	200 W	100 VA	200 VA
		Without Neutral	5 - 100 VA	5 - 200 VA	5 - 100 W	5 - 200 W	5 - 100 VA	5 - 200 VA
	5 743 36	With Neutral	100 VA	200 VA	100 W	200 W	100 VA	200 VA
		Without Neutral	5 - 100 VA	5 - 200 VA	5 - 100 W	5 - 200 W	5 - 100 VA	5 - 200 VA
	5 743 35	With Neutral	100 VA	200 VA	100 W	200 W	100 VA	200 VA
		Without Neutral	5 - 100 VA	5 - 200 VA	5 - 100 W	5 - 200 W	5 - 100 VA	5 - 200 VA

	Cat.Nos	Universal						
		LEDs and CFLs		Halogen/Incandescent lamps		LEDs, CFLs, halogen, fluorescent tube with ferromagnetic or electronic transformer		
		110 V~	230 V~	110 V~	230 V~	110 V~	230 V~	
Motion sensors	Without Neutral	5 740 09A	2 - 50 VA	2 - 100 VA	2 - 50 W	2 - 150 W	2 - 75 VA	2 - 150 VA
		5 740 59A						
	With Neutral	5 740 47A	0 - 250 VA	0 - 500 VA	0 - 1000 W	0 - 2000 W	0 - 500 VA	0 - 1000 VA
		5 740 97A						
		5 741 41A						
		5 741 40A						

	Cat.Nos	Universal								
		Dimmable LEDs and CFLs		Halogen/Incandescent lamps		Halogen and fluorescent tube with ferromagnetic transformer		LEDs, CFLs, halogen, and fluorescent tube with electronic transformer		
		110 V~	230 V~	110 V~	230 V~	110 V~	230 V~	110 V~	230 V~	
Dimmers for all dimmable loads	Without Neutral	5 722 39A	3 - 75 VA	3 - 125 VA	3 - 75 W	3 - 125 W	3 - 75 VA	3 - 125 VA	3 - 75 VA	3 - 125 VA
		5 727 39A								
		5 729 37A								
		5 729 36A								
	With Neutral	5 741 89A	0 - 75 VA	0 - 150 VA	0 - 75 W	0 - 150 W	0 - 75 VA	0 - 150 VA	0 - 75 VA	0 - 150 VA
		5 741 90A								
		5 741 91A								
		5 741 88A								

	Cat.Nos	Universal						
		Halogen/Incandescent lamps		Halogen with ferromagnetic transformer		Halogen with electronic transformer		
		110 V~	240 V~	110 V~	240 V~	110 V~	240 V~	
Rotary dimmers	Without Neutral	5 722 13	20 - 200 W	40 - 400 W	20 - 200 VA	40 - 400 VA	-	-
		5 727 13						
		5 700 53						
		5 710 53						
		5 735 01	60 - 500 W	60 - 1000 W	60 - 500 VA	60 - 1000 VA	60 - 300 VA	60 - 600 VA
		5 737 01						
Dimmers 1 - 10 V	With Neutral	5 722 38	-	-	-	-	20 - 300 VA	20 - 600 VA
		5 727 38						
		5 729 39						
		5 729 39						
		5 729 38						