

XL³ S 630

equipment for mounting DPX³ 630 and DRX 630 on a plate



Selection chart p. 326 to 331

Pack	Cat.Nos		Fixing plates for DPX ³ 630 and DRX 630 - horizontal mounting
	3P	4P	
1	3 387 00	3 387 01	For 16-module enclosure
1	3 387 03	3 387 04	For 24-module enclosure
1	3 387 06	3 387 07	For 36-module enclosure


Pack	Cat.Nos		Fixing plates for DPX ³ 630 and DRX 630 - vertical mounting
	3P/4P		
1	3 387 20		Without e.l.c.b For 16-module enclosure
1	3 387 24		For 24-module enclosure
1	3 387 27		For 36-module enclosure
	4P with e.l.c.b		With e.l.c.b
1	3 387 21		For 16-module enclosure
1	3 387 25		For 24-module enclosure
1	3 387 28		For 36-module enclosure

Pack	Cat.Nos		Fixing plates for DPX ³ 630 with rotary handle - vertical mounting
	3P/4P		
1	3 383 86		For 16-module enclosure
1	3 383 87		For 24-module enclosure
1	3 383 88		For 36-module enclosure

Pack	Cat.Nos		Fixing plates for DPX ³ 630 with motor-driven handle - vertical mounting
	3P/4P		
1	3 383 89		For 16-module enclosure
1	3 383 90		For 24-module enclosure
1	3 383 91		For 36-module enclosure


Pack	Cat.Nos		Fixing plates for DPX ³ 630 transfer switch version - vertical mounting
	3P/4P		
1	3 384 80		Transfer switch without motor-driven handle For 24-module enclosure
1	3 384 81		For 36-module enclosure

Pack	Cat.Nos		Faceplates for DPX ³ 630 and DRX 630 - horizontal mounting
	3P	4P	
1	3 387 50	3 387 51	Height: 3P: 150 mm / 4P: 200 mm
1	3 387 53	3 387 54	For 16-module enclosure
1	3 387 56	3 387 57	For 24-module enclosure
			For 36-module enclosure




Pack	Cat.Nos	With e.l.c.b
1	4P with e.l.c.b 3 387 58	Height: 200 mm For 36-module enclosure

Pack	Cat.Nos		Faceplates for DPX ³ 630 and DRX 630 - vertical mounting
	3P/4P		
1	3 387 70		Fixed with 1/4 turn screws or screws
1	3 387 74		Without e.l.c.b Height: 400 mm
1	3 387 77		For 16-module enclosure
			For 24-module enclosure
			For 36-module enclosure



Pack	Cat.Nos	With e.l.c.b
1	4P with e.l.c.b 3 387 71	Height: 600 mm
1	3 387 75	For 16-module enclosure
1	3 387 78	For 24-module enclosure
		For 36-module enclosure

Pack	Cat.Nos		Faceplates for DPX ³ 630 with rotary or motor-driven handle - vertical mounting
	3P/4P		
1	3 383 92		Fixed with 1/4 turn screws or screws
1	3 383 93		Height: 400 mm
1	3 383 94		For 16-module enclosure
			For 24-module enclosure
			For 36-module enclosure



Pack	Cat.Nos		Faceplates for DPX ³ 630 transfer switch - vertical mounting
	3P/4P		
1	3 384 84		Fixed with 1/4 turn screws or screws
1	3 384 85		Without motor-driven handle Height: 400 mm
			For 24-module enclosure
			For 36-module enclosure

