



5 721 38A + plate 5 751 10A



5 721 39 + plate 5 751 70



5 726 62A + plate 5 754 71



5 710 94 + plate 5 754 46

Mechanisms supplied with rocker plates, to be equipped with special plates
Support frame not needed

Pack	Cat.Nos	Multistandard switched socket outlets 16 A - 250 V~ / 15 A - 127 V~ with USB charger
1	5 721 38A	Shuttered for child safety 2P+E - 1-gang USB Type-A 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.07 W ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 726 38A	
1	5 710 83A	
1	5 700 83A	
1	5 721 62A	2P+E - 1-gang USB Type-C 18 W Fast charge feature: USB Type-C Power Delivery Consumption in passive mode < 0.07 W ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 726 62A	
1	5 722 62A	
1	5 722 64A	
1	5 721 39	2 x 2P+E - 2-gang USB Type-A + Type-C 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.07 W ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 726 39	
1	5 710 84	
1	5 700 84	
1	5 722 87	2 x 2P+E - 2-gang USB Type-A + Type-C 27 W Fast charge feature: USB Type-C Power Delivery Consumption in passive mode < 0.07 W ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 727 92	
1	5 700 86	
1	5 710 94	

Pack	Cat.Nos	Special plates for Arteor multistandard socket outlets with USB charger
5	5 751 10A	For 1-gang switched socket outlet USB Type-A 3 A - 5 V_{DC} - 15 W ○ Neutral - White ● Soft Alu ● Graphite ● Magnesium ● Champagne ● Dark Bronze ● Brushed Metal - Stainless Steel
5	5 751 44A	
5	5 751 43A	
5	5 751 45A	
5	5 751 46A	
5	5 751 47A	
1	5 751 16A	For 1-gang switched socket outlet USB Type-C 18 W ○ Neutral - White ● Soft Alu ● Graphite ● Magnesium ● Champagne ● Dark Bronze ● Brushed Metal - Stainless Steel
5	5 754 67	
5	5 754 68	
5	5 754 69	
5	5 754 71	
5	5 754 72	
5	5 754 73	For 2-gang switched socket outlet USB Type-A + Type-C 3 A - 5 V_{DC} - 15 W ○ Neutral - White ● Soft Alu ● Graphite ● Magnesium ● Champagne ● Dark Bronze ● Brushed Metal - Stainless Steel
5	5 751 70	
5	5 751 72	
5	5 751 71	
5	5 751 73	
5	5 751 74	
5	5 751 75	For 2-gang switched socket outlet USB Type-A + Type-C 27 W ○ Neutral - White ● Soft Alu ● Graphite ● Magnesium ● Champagne ● Dark Bronze ● Brushed Metal - Stainless Steel
5	5 754 44	
5	5 754 46	
5	5 754 45	
5	5 754 47	
5	5 754 48	
5	5 754 49	
1	5 754 51	