



## Equipment for XL<sup>3</sup> 4000

for mounting on fixed plate: DPX<sup>3</sup> 160 and DPX<sup>3</sup> 250



## Equipment for XL<sup>3</sup> 4000

for mounting on fixed plate: DPX<sup>3</sup> 125 HP



Selection chart p. 376 to 379

Pack	Cat.Nos	Plates for fixed version DPX <sup>3</sup> 160/250 with front terminals
1	24 modules 0 206 11   36 modules 0 206 61	Direct fixing on functional uprights <b>Devices in vertical position</b> Equipped with a rail  for fixing DPX <sup>3</sup> . The DPX <sup>3</sup> must be equipped with a fixing plate Cat.Nos 4 210 68/69/71/72 or plate for manual supply inverter Cat.No 4 210 58. Designed for simultaneous mounting of DPX <sup>3</sup> 160/250 and modular equipment (with spacer Cat.No 0 262 99)
1	0 206 08	Plate for DPX <sup>3</sup> with direct rotary handle. The DPX <sup>3</sup> must be equipped with a fixing plate Cat.Nos 4 210 68/69
1	0 206 13	Plate for motor-driven transfer switch. The transfer switch must be equipped with a fixing plate Cat.Nos 4 210 58
1	24 modules 0 206 15	<b>Devices in horizontal position</b> For cut-out protection for cable passing, use seal Cat.No 0 202 40 (p. 394) For 1 DPX <sup>3</sup> 160
1	0 206 17	For 1 DPX <sup>3</sup> 250

Pack	Cat.Nos	Metal faceplates for devices in vertical position
1	24 modules 0 208 10 <sup>1</sup>	<b>For DPX<sup>3</sup> without direct rotary handle</b> 1/4 turn With captive screws With captive screws for DPX <sup>3</sup> 250 with terminal shields 
1	0 209 10 <sup>2</sup>	
1	0 209 27	
1	24 modules 0 208 05 <sup>1</sup>	<b>For DPX<sup>3</sup> with direct rotary handle</b> 1/4 turn With captive screws 
1	0 209 05 <sup>2</sup>	

Pack	Cat.Nos	Metal faceplates for devices in horizontal position
1	0 208 13 <sup>1</sup>	<b>For DPX<sup>3</sup> 160 without motor-driven handle</b> 1/4 turn With captive screws 
1	0 209 13 <sup>2</sup>	
1	0 208 17 <sup>1</sup>	<b>For DPX<sup>3</sup> 160 with motor-driven handle and DPX<sup>3</sup> 250</b> 1/4 turn With captive screws 
1	0 209 17 <sup>2</sup>	

1: For fastening and sealing  
2: Hinges Cat.No 0 209 59 (p. 394) available as an option

Selection chart p. 376 to 379

Pack	Cat.Nos	Plates for DPX <sup>3</sup> 125 HP, with front terminals
1	24 modules 0 213 00	Direct fixing on functional uprights <b>Devices in vertical position</b> For 1 to 3 DPX <sup>3</sup> 125 HP
1	0 213 01	<b>Devices in horizontal position</b> For 1 DPX <sup>3</sup> 125 HP
1	24 modules 0 213 02	<b>Metal faceplates for devices in vertical position</b> <b>For 1 to 3 DPX<sup>3</sup> 125 HP</b> With captive screws 
1	24 modules 0 213 03	<b>Metal faceplates for devices in horizontal position</b> <b>For 1 DPX<sup>3</sup> 125 HP</b> With captive screws 