5 720 91 | 5 722 72 | 5 722 83 | 5 722 70 | 5 722 84 | 5 722 76

Support frame and plate selection charts **p. 594-603**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 585) and plates (p. 594-603)

Jack sockets 3.5 mm

3.5 mm Jack connectors can be used to create audio links

Preterminated sockets - 1 module
Equipped with cord, length 15 cm

Pack	Cat.Nos	
1	5 720 91	White
1	5 725 91	Magnesium
1	5 725 59	Champagne
1	5 725 55	Soft Alu

4 screw-type female 3.5 mm Jack socket - 1 module

1	5 722 74	White
1	5 727 74	Magnesium
1	5 724 91	Champagne
1	5 724 90	Soft Alu

Solder-type female 3.5 mm Jack socket - 1 module

1	5 722 78	White

Female 2 RCA sockets

Provide the stereo audio link for any peripheral device such as a DVD drive, camera, video recorder

Preterminated - 1 module
Equipped with a 15 cm cord

Pack	Cat.Nos	
1	5 720 92	White
1	5 725 92	Magnesium
1	5 724 79	Champagne
1	5 724 75	Soft Alu

Connection on screw terminals - 1 module

1	5 722 72	White
1	5 727 72	Magnesium
1	5 724 95	Champagne
1	5 724 94	Soft Alu

Female 3 RCA sockets

Provide the stereo audio link for any peripheral device such as a DVD drive, camera, video recorder

Connection on screw terminals - 2 modules

Pack	Cat.Nos	
1	5 722 73	White
1	5 727 73	Magnesium
1	5 724 97	Champagne
1	5 724 96	Soft Alu

3-pole XLR sockets

For the stereo connection of any peripheral, microphone, mixing console
Recommended cable:
1 audio pair 0.14 to 0.5 mm² shielded
Max. cable length: 50 m (beyond this an audio amplifier is recommended)
2 modules

XLR female

Pack	Cat.Nos	
1	5 722 83	White
1	5 727 83	Magnesium
1	5 724 99	Champagne
1	5 724 98	Soft Alu

XLR male

1	5 722 77	White

Loudspeaker sockets

4 mm² terminals

1 module

Pack	Cat.Nos	
10	5 722 70	White
10	5 727 70	Magnesium
10	5 726 97	Champagne
10	5 726 96	Soft Alu

2 modules

10	5 722 80	White
10	5 727 80	Magnesium
10	5 726 99	Champagne
10	5 726 98	Soft Alu

Attenuators

100 V - 25 W
Allow to adjust power to 25 W from a balanced 100 V loudspeaker line
2 modules

Pack	Cat.Nos	
1	5 722 84	White
1	5 727 84	Magnesium

Female BNC 75 sockets

Provide the composite video link for any peripheral device such as a DVD drive, camera, video recorder, etc
Connection on screw terminals - 1 module

1	5 722 76	White
1	5 727 76	Magnesium