

Arteor™ with Netatmo - International

connected wireless scene switches

Step 2: Connected products



Home + Control



5 742 08



5 742 87



5 742 70



5 744 30



Support frame and plate selection charts **p. 594 to 603**

Used to complete your connected installation, require prior installation of a gateway pack for connected installation
Zigbee Certified Product

Pack	Cat.Nos	Wake up/Sleep wireless switches
		Used to add 2 extra scenes to a connected installation Preset Wake up/Sleep life scenes which can be customised in the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply LED function for low battery indication
		Surface-mounting version, 1-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594-603)
1	5 742 08	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 26	
1	5 742 35	
1	5 742 17	
		Flush-mounting version, 1 module Mechanism supplied with cover plate, to be equipped with support frames (p. 614) and plates (p. 594-603) Can be installed in a flush-mounting box depth 35 mm Allows aesthetic consistency for modular installation
1	5 742 73	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 90	
1	5 743 28	
1	5 742 98	

Pack	Cat.Nos	Wake up/Sleep wireless batteryless switch
		Extra-slim, maintenance-free device without any battery Used to add 2 extra scenes to a connected installation Energy harvesting mechanism that generates by itself the energy required for the switching process Qualified for 1 million cycles Smooth and silent switching Preset Wake up/Sleep life scenes which can be customised in the Home + Control App.
		1-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594-603)
1	5 742 87	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 743 22	
1	5 748 36	
1	5 742 93	

Pack	Cat.Nos	Home/Away wireless master switches
		Used to add an extra Home/Away wireless master switch Work in the same way as the Home/Away wireless master switch included in the gateway pack Home/Away life scenes can be customised in the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply LED function for low battery indication
		Surface-mounting version, 1-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594-603)
1	5 742 06	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 24	
1	5 742 33	
1	5 742 15	
		Flush-mounting version, 1 module Mechanism supplied with cover plate, to be equipped with support frames (p. 614) and plates (p. 594-603) Can be installed in a flush-mounting box depth 35 mm Allows aesthetic consistency for modular installation
1	5 742 70	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 79	
1	5 743 27	
1	5 742 97	

Pack	Cat.Nos	Home/Away wireless batteryless master switch
		Extra-slim, maintenance-free device without any battery Used to add an extra Home/Away wireless master switch Work in the same way as the Home/Away wireless master switch included in the gateway pack Energy harvesting mechanism that generates by itself the energy required for the switching process Qualified for 1 million cycles Smooth and silent switching Home/Away life scenes can be customised in the Home + Control App.
		1-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594-603)
1	5 744 30	<ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 744 31	
1	5 744 32	
1	5 744 33	