

Atlantic, Atlantic stainless steel and Marina cabinets equipment (continued)



0 363 13



0 475 45



Metal Atlantic cabinet equipped with document holder
Cat.No 0 365 82


Cabinet and equipment selection chart **p. 414-415**

Pack	Cat.Nos	Hinged glass doors					
		IP 54 Anodised aluminium frame Polycarbonate transparent window, 3 mm stick Neoprene seal 455 key lock. 150° opening Supplied complete with drilling template For devices on front panels. Protect the devices and prevent accidental operation					
		Width (mm)	Height (mm)	External dim. Width (mm)	Window Height (mm)	Window Depth (mm)	Usable Depth (mm)
1	0 475 45	300	400	50	230	330	42
1	0 475 46	400	400	50	330	330	42
1	0 475 47	500	500	50	430	430	42

		Copper bars				
		Copper bars with tapped holes				
		Cross-section (mm)	Permis I (A)	Tapped holes		Length (mm)
				Ø mm	Pitch	
10	0 373 88	12 x 2	110	M5	18	990
10	0 373 89	12 x 4	160	M5	18	990
100	0 373 65 ¹	Connectors for bars with tapped holes				
		1 or 2 conductor from 1.5 to 10 mm ² (supplied with Ø5 mm screws)				
		Non perforated copper bar				
		Cross-section (mm)	Permis I (A)	Length (mm)		
10	0 373 49	12 x 4	180	991.5		
100	0 373 60	Connectors for bar Cat.No 0 373 49				
		1.5 to 4 mm ²				
10	0 373 61	6 to 16 mm ²				
10	0 373 62	10 to 35 mm ² (supplied with M6 CHC Ø5 mm)				



Pack	Cat.Nos	Door contact	
1	0 363 13	For example, to cut off the air conditioning and the lighting supply as soon as the enclosure or cabinet door is opened 3 A - 240 V 1 NC contact + 1 NO contact For Atlantic and Marina cabinets Supplied with fixing lug	
		Self adhesive document holder (for plans)	
		Open - RAL 7035	
		External dimensions	
		Width (mm)	Height (mm)
20	0 365 80	340	235
20	0 365 81	260	165
		Internal dimensions	
		Width (mm)	Height (mm)
		Depth (mm)	
		310	200
		130	18
1	0 365 82	Closed - RAL 7035	
		Rigid plastic - IP 50	
		Internal dimensions: 324 x 120 x 18 mm	
10	0 097 99	Transparent	
		Flexible plastic - A4 - 305 x 220 mm	
1	0 363 86 ²	Door stop for Atlantic metal cabinets	
		Allows door stop at 90° Supplied with screws	



1: Protective conductor per connector (art. 12 of French decree of 14/11/89)
2: For Atlantic metal cabinets only