Atlantic, Atlantic stainless steel and Marina cabinets

chassis for customer assembly





Pack	Cat.Nos	
		Functional and faceplate support uprights for plastic faceplates
		For Atlantic, Atlantic stainless steel and Marina cabinets Can take: ⌙ rails depth 15 mm, solid plates, Lina 12.5 and Lina 25 plates and plastic faceplates
1	4 330 20	For cabinets 700 x 500 mm
1	4 330 21	For cabinets 800 x 600 mm
1	4 330 22	For cabinets 800 x 800 mm
1	4 330 23	For cabinets 1000 x 600 mm
1	4 330 24	For cabinets 1000 x 800 mm
1	4 330 25	For cabinets 1200 x 800 mm
		Plastic faceplates for modular equipment
		For Atlantic, Atlantic stainless steel and Marina cabinets RAL 7035 Supplied with ⌙ rails depth 15 mm Fix onto faceplate support uprights for plastic faceplates Cat.Nos 4 330 20/21/22/23/24/25 Adjustable rail depth: 45, 60 or 75 mm
		Height 150 mm
1	4 330 50	For cabinets width 500 mm (19 modules/row)
1	4 330 51	For cabinets width 600 mm (25 modules/row)
1	4 330 52	For cabinets width 800 mm (36 modules/row)
		Height 300 mm
1	4 330 60	For cabinets width 500 mm (19 modules/row)
1	4 330 61	For cabinets width 600 mm (25 modules/row)
1	4 330 62	For cabinets width 800 mm (36 modules/row)
		Plastic solid faceplates
		For Atlantic, Atlantic stainless steel and Marina cabinets RAL 7035 Fix onto faceplate support uprights for plastic faceplates Cat.Nos 4 330 20/21/22/23/24/25
		Height 150 mm
1	4 330 53	For cabinets width 500 mm
1	4 330 54	For cabinets width 600 mm
1	4 330 55	For cabinets width 800 mm
		Height 300 mm
1	4 330 63	For cabinets width 500 mm
1	4 330 64	For cabinets width 600 mm
1	4 330 65	For cabinets width 800 mm

Pack	Cat.Nos	
		Functional and faceplate support uprights for metal faceplates
		For Atlantic and Atlantic stainless steel cabinets Can take: ⌙ rails depth 15 mm, solid plates, Lina 12.5 and Lina 25 plates and metal faceplates
1	4 330 30	For cabinets 700 x 500
1	4 330 31	For cabinets 800 x 600
1	4 330 32	For cabinets 800 x 800
1	4 330 33	For cabinets 1000 x 600
1	4 330 34	For cabinets 1000 x 800
1	4 330 35	For cabinets 1200 x 800
		Metal faceplates for modular equipment
		For Atlantic and Atlantic stainless steel cabinets RAL 7035 Supplied with ⌙ rails depth 15 mm Fix onto faceplate support uprights for metal faceplates Cat.Nos 4 330 30/31/32/33/34/35 Adjustable rail depth: 45, 60 or 75 mm
		Height 150 mm
1	4 330 73	For cabinets width 500 mm (19 modules/row)
1	4 330 74	For cabinets width 600 mm (25 modules/row)
1	4 330 75	For cabinets width 800 mm (36 modules/row)
		Height 200 mm
1	4 330 80	For cabinets width 500 mm (19 modules/row)
1	4 330 81	For cabinets width 600 mm (25 modules/row)
1	4 330 82	For cabinets width 800 mm (36 modules/row)
		Height 300 mm
1	4 330 90	For cabinets width 500 mm (19 modules/row)
1	4 330 91	For cabinets width 600 mm (25 modules/row)
1	4 330 92	For cabinets width 800 mm (36 modules/row)
		Solid metal faceplates
		For Atlantic and Atlantic stainless steel cabinets RAL 7035 Fix onto faceplate support uprights for metal faceplates Cat.Nos 4 330 30/31/32/33/34/35
		Height 50 mm
1	4 330 70	For cabinets width 500 mm
1	4 330 71	For cabinets width 600 mm
1	4 330 72	For cabinets width 800 mm
		Height 150 mm
1	4 330 76	For cabinets width 500 mm
1	4 330 77	For cabinets width 600 mm
1	4 330 78	For cabinets width 800 mm