


Arteor™ with Netatmo - International

connected wireless scene switches and curtain/roller blind controls

Step 2: Connected products



Home + Control



5 744 40



5 742 25



5 742 74






5 744 20






Support frame and plate selection charts p. 594 to 603

Used to complete your connected installation, require prior installation of a gateway pack for connected installation
Zigbee Certified Product

Pack	Cat.Nos	4 scenes wireless switches
		Used to add 4 customised scenes to a connected installation Scenes can be customised in the Home + Control App. Possibility to assign personalized names and to associate icons to the scenes in the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply
1	5 743 12	Surface-mounting version, 2-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594 to 603) LED function for low battery indication  <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 743 14	
1	5 743 15	
1	5 743 13	
1	0 676 95	Pocket remote control Can be attached to a keyring ● Magnesium 

Pack	Cat.Nos	4 scenes wireless batteryless switch
		Extra-slim, maintenance-free device without any battery Used to add 4 customised scenes to a connected installation Energy harvesting mechanism that generates by itself the energy required for the switching process Qualified for 1 million cycles Smooth and silent switching Scenes can be customised in the Home + Control App. Possibility to assign personalized names and to associate icons to the scenes in the Home + Control App.
1	5 744 40	2-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594 to 603)  <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 744 41	
1	5 744 42	
1	5 744 43	

Pack	Cat.Nos	Curtain/roller blind wireless switches
		Used for remote control or centralization of up to 20 wired roller blind switches Pair by tapping the selected roller blind switch(es) or by using the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply LED function for low battery indication
1	5 742 07	Surface-mounting version, 1-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594 to 603)  <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 25	
1	5 742 34	
1	5 742 16	
1	5 742 74	Flush-mounting version, 1 module Mechanism supplied with cover plate, to be equipped with support frames and plates (p. 594 to 603) Can be installed in a flush-mounting box depth 35 mm Allows aesthetic consistency for modular installation  <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 742 95	
1	5 743 29	
1	5 742 99	

Pack	Cat.Nos	Curtain/roller blind wireless batteryless switch
		Extra-slim, maintenance-free device without any battery Used for remote control or centralization of up to 20 wired roller blind switches Energy harvesting mechanism that generates by itself the energy required for the switching process Qualified for 1 million cycles Smooth and silent switching Pair by tapping the selected roller blind switch(es) or by using the Home + Control App.
1	5 744 20	2-gang Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594 to 603)  <ul style="list-style-type: none"> ○ White ● Magnesium ● Champagne ● Soft Alu
1	5 744 21	
1	5 744 22	
1	5 744 23	

Pack	Cat.Nos	Accessory
1	0 648 71	Pack of 3 x 4 extra removable stickers for fixing a wireless control