


Atlantic, Atlantic stainless steel and Marina cabinets - chassis for customer assembly (continued)

Atlantic, Atlantic stainless steel and Marina cabinets - chassis for customer assembly



Pack Cat.Nos Solid metal faceplates (continued)

Pack	Cat.Nos	Description
		RAL 7035 Fix onto faceplate support uprights for metal faceplates Cat.Nos 4 330 30/31/32/33/34/35
1	4 330 83	Height 200 mm For cabinets width 500 mm
1	4 330 84	For cabinets width 600 mm
1	4 330 85	For cabinets width 800 mm
		Height 300 mm
1	4 330 93	For cabinets width 500 mm
1	4 330 94	For cabinets width 600 mm
1	4 330 95	For cabinets width 800 mm

Pack	Cat.Nos	Description
1	4 330 99	Fixing lugs Used to mount and adjust the depth of rails depth 15 mm, solid plates, or Lina 12.5 and Lina 25 plates on functional uprights of chassis for customer assembly If mounting plates, order 2 kits Kit of 2 lugs

Pack	Cat.Nos	Description
1	4 330 45	Mounting plates For mounting power equipment such as DPX ³ 160, Vistop 160 A in cabinets width 600 mm
1	4 330 46	For mounting 1, 2 or 3 DPX ³ 160, DPX ³ 250 and Vistop 160 A power devices in cabinets width 800 mm

Cabinet faceplate height

Cabinet height (mm)	Usable height (mm)	
	Plastic Faceplates	Metal Faceplates
700	600	650
800	750	750
1000	900	950
1200	1050	1150

Selection guide

Cabinet H x W (mm)	700 x 500	800 x 600	800 x 800	1000 x 600	1000 x 800	1200 x 800
	4 330 30	4 330 31	4 330 32	4 330 33	4 330 34	4 330 35
	4 330 70	4 330 71	4 330 72	4 330 71	4 330 72	4 330 72
	4 330 73	4 330 74	4 330 75	4 330 74	4 330 75	4 330 75
	4 330 76	4 330 77	4 330 78	4 330 77	4 330 78	4 330 78
	4 330 80	4 330 81	4 330 82	4 330 81	4 330 82	4 330 82
	4 330 83	4 330 84	4 330 85	4 330 84	4 330 85	4 330 85
	4 330 90	4 330 91	4 330 92	4 330 91	4 330 92	4 330 92
	4 330 93	4 330 94	4 330 95	4 330 94	4 330 95	4 330 95
	4 330 20	4 330 21	4 330 22	4 330 23	4 330 24	4 330 25
	4 330 50	4 330 51	4 330 52	4 330 51	4 330 52	4 330 52
	4 330 53	4 330 54	4 330 55	4 330 54	4 330 55	4 330 55
	4 330 60	4 330 61	4 330 62	4 330 61	4 330 62	4 330 62
	4 330 63	4 330 64	4 330 65	4 330 64	4 330 65	4 330 65