

# Arteor™ with Netatmo - British standard

connected wireless light controls

## Step 2: Connected products



Home + Control



5 746 63



5 746 73



5 743 25



5 744 34

Plate selection charts p. 594 to 603

Used to complete your connected installation, require prior installation of a gateway pack for connected installation  
Zigbee Certified Product

Pack	Cat.Nos	Wireless light switches
		Used to add an extra control for wired switches, micromodules, socket outlets, cable outlets Easy pairing by tapping the wired product or by using the Home + Control App. Supplied with CR2032 3V long-life battery for power supply Easy access to the battery for maintenance LED function for low battery indication Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594 to 603)
		<b>1-gang</b> Controls up to 20 wired products
1	5 746 63	<ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5 746 64	
1	5 746 66	
1	5 746 65	
		<b>2-gang</b> Controls up to 2x20 wired products
1	5 746 67	<ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5 746 68	
1	5 746 70	
1	5 746 69	
		<b>3-gang</b> Controls up to 3x20 wired products
1	5 746 71	<ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5 746 72	
1	5 746 74	
1	5 746 73	

Pack	Cat.Nos	Wireless batteryless light switches
		Extra-slim, maintenance-free device without any battery Used to add an extra control for wired switches, micromodules, socket outlets and cable outlets Energy harvesting mechanism that generates by itself the energy required for the switching process Qualified for 1 million cycles Smooth and silent switching Easy pairing by tapping the wired product (switches, micromodules, socket outlets) or by using the Home + Control App. Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594 to 603)
		<b>1-gang</b> Controls up to 20 wired products
1	5 742 39	<ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5 743 24	
1	5 742 55	
1	5 742 10	
		<b>2-gang</b> Controls up to 2x20 wired products
1	5 742 89	<ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5 743 25	
1	5 748 38	
1	5 742 96	

Pack	Cat.Nos	Wireless switches for multicolour lighting
		Allow to directly control up to 20 Zigbee 3.0 compatible multi-colour lighting (e.g. Ledvance Smart+ Zigbee, Philips Hue...) To be associated with the lighting in the Home + Control App. Allow ON/OFF and dimming control of 3 light moods which have to be preset in the Home + Control App. Supplied with CR2032 3 V long-life battery for power supply LED function for low battery indication Not compatible with Wi-Fi lighting
		<b>Surface-mounting version, 2-gang</b> Supplied with cover plate, multi-standard support frame (with removable fins) and removable stickers for fixing the control unit on any substrate To be equipped with 2-module plates (p. 594 to 603)
1	5 744 34	<ul style="list-style-type: none"> <li>○ White</li> <li>● Magnesium</li> <li>● Champagne</li> <li>● Soft Alu</li> </ul>
1	5 744 35	
1	5 744 36	
1	5 744 37	