

Green'up™ One charging stations

for electric vehicle charging



Green'up™ One charging stations

for electric vehicle charging



CHARGER CONTROL

With power adjustment function

With integrated 6 mA \approx protection



0 570 16



0 570 18



0 570 18 + 0 570 16

Recommended for individual home installations

Integrated 6 mA DC detection

For charging all electric vehicles (equipped with single-phase and three-phase chargers) and plug-in hybrids in Mode 3 in complete safety. Compliant with standard IEC 61851-1

Charging station power can be adjusted with adapted protection devices and power supply circuits. Local wireless communication via embedded Bluetooth for configuration and control of charging station via smartphone or tablet using the IOS or Android CHARGER CONTROL App. (power limitation, ON/OFF management, status, LED brightness, load management settings)

Equipped with:

- a 5 m cord, plug holder and Type 2 plug (single-phase or three-phase operation) with pilot wire (Mode 3)

- LED indicating the status of the charge (green / blue / red / yellow)

Connected and protected from the electrical panel via 1 protected dedicated line


Remote ON/OFF control option (volt-free contact input 12 V=).

Compatible with connected dry contact Cat.No 4 121 73 (p. 113)


controlled remotely using a smartphone via the Home + Control App.

Pack	Cat.Nos	Plastic single-phase charging stations - Mode 3
		IP 54 - IK 10 For charging 1 vehicle Wall mounting charging stations. Can be equipped with pedestal Cat.No 0 570 18 for fixing to the ground
1	0 570 10	3.7 kW - 16 A (adjustable from 6 A to 16 A) Without integrated protection
1	0 570 11	With integrated protection (RCBO) : 16 A - 30 mA
1	0 570 12	7.4 kW - 32 A (adjustable from 6 A to 32 A) Without integrated protection
1	0 570 13	With integrated protection (RCBO) : 32 A - 30 mA
		Plastic three-phase charging stations - Mode 3
		IP 54 - IK 10 For charging 1 vehicle Wall mounting charging stations. Can be equipped with pedestal Cat.No 0 570 18 for fixing to the ground
1	0 570 14	11 kW - 16 A (adjustable from 6 A to 16 A) Without integrated protection
1	0 570 15	With integrated protection (RCBO) : 16 A - 30 mA
1	0 570 16	22 kW - 32 A (adjustable from 6 A to 32 A) Without integrated protection
1	0 570 17	With integrated protection (RCBO) : 32 A - 30 mA
		Metal pedestal for Green'up One charging stations
1	0 570 18	For fixing charging stations to the ground Can take one or two charging stations

Dimensions



Minimum space needed for operation and maintenance



Comply with the national regulations and site requirements