


Arteor™ mechanical switches

square version



Support frame and plate selection charts **p. 594-603**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 585) and plates (p. 594-603)

Pack	Cat.Nos	Switches 10 AX - 250 V~
10	5 720 04	1-way switch ○ White - 1 module
10	5 725 04	● Magnesium - 1 module
10	5 700 04	● Champagne - 1 module
10	5 710 04	● Soft Alu - 1 module
10	5 724 50	● Red - 1 module
10	5 720 34	2-way switch ○ White - 2 modules
10	5 725 34	● Magnesium - 2 modules
10	5 700 34	● Champagne - 2 modules
10	5 710 34	● Soft Alu - 2 modules
10	5 720 05	2-way switch ○ White - 1 module
10	5 725 05	● Magnesium - 1 module
10	5 700 05	● Champagne - 1 module
10	5 710 05	● Soft Alu - 1 module
10	5 720 35	2-way switch with indicator ○ White - 2 modules
10	5 725 35	● Magnesium - 2 modules
10	5 700 35	● Champagne - 2 modules
10	5 710 35	● Soft Alu - 2 modules
10	5 720 06	2-way switch with indicator To be equipped with LED (p. 565) ○ White - 1 module
10	5 725 06	● Magnesium - 1 module
10	5 721 75	● Champagne - 1 module
10	5 721 74	● Soft Alu - 1 module
5	5 720 36	2-way switch with indicator and label-holder To be equipped with LED (p. 565) ○ White - 2 modules
5	5 725 36	● Magnesium - 2 modules
5	5 721 77	● Champagne - 2 modules
5	5 721 76	● Soft Alu - 2 modules
5	5 720 08	Intermediate switch ○ White - 1 module
5	5 725 08	● Magnesium - 1 module
5	5 700 08	● Champagne - 1 module
5	5 710 08	● Soft Alu - 1 module
10	5 720 38	2-way switch with indicator and label-holder To be equipped with LED (p. 565) ○ White - 2 modules
10	5 725 38	● Magnesium - 2 modules
10	5 721 66	● Champagne - 2 modules
10	5 721 65	● Soft Alu - 2 modules
10	5 720 40	Double pole switch ○ White - 2 modules
5	5 725 40	● Magnesium - 2 modules
5	5 721 79	● Champagne - 2 modules
5	5 721 78	● Soft Alu - 2 modules

Pack	Cat.Nos	Switches 20 AX - 250 V~
10	5 720 09	1-way switch ○ White - 1 module
10	5 725 09	● Magnesium - 1 module
10	5 700 09	● Champagne - 1 module
10	5 710 09	● Soft Alu - 1 module
10	5 720 41	2-way switch ○ White - 2 modules
10	5 725 41	● Magnesium - 2 modules
10	5 723 81	● Champagne - 2 modules
10	5 723 80	● Soft Alu - 2 modules
10	5 720 10	2-way switch ○ White - 1 module
10	5 725 10	● Magnesium - 1 module
10	5 700 10	● Champagne - 1 module
10	5 710 10	● Soft Alu - 1 module
10	5 720 11	2-way switch with indicator To be equipped with LED (p. 565) ○ White - 1 module
5	5 725 11	● Magnesium - 1 module
5	5 723 83	● Champagne - 1 module
5	5 723 82	● Soft Alu - 1 module
10	5 720 42	2-way switch with indicator and label-holder To be equipped with LED (p. 565) ○ White - 2 modules
5	5 725 42	● Magnesium - 2 modules
5	5 723 85	● Champagne - 2 modules
5	5 723 84	● Soft Alu - 2 modules
10	5 720 43	1-way switch - 3-gang ○ White - 2 modules
10	5 725 43	● Magnesium - 2 modules
10	5 723 87	● Champagne - 2 modules
10	5 723 86	● Soft Alu - 2 modules
10	5 720 44	2 x 2-way switch + 1-way switch - 3-gang ○ White - 2 modules
10	5 725 44	● Magnesium - 2 modules
10	5 723 89	● Champagne - 2 modules
10	5 723 88	● Soft Alu - 2 modules
5	5 720 13	1-way double pole switch ○ White - 1 module
5	5 725 13	● Magnesium - 1 module
5	5 721 83	● Champagne - 1 module
5	5 721 82	● Soft Alu - 1 module
5	5 724 51	● Red - 1 module
10	5 720 46	2-way switch with indicator and label-holder To be equipped with LED (p. 565) ○ White - 2 modules
10	5 725 46	● Magnesium - 2 modules
10	5 721 85	● Champagne - 2 modules
10	5 721 84	● Soft Alu - 2 modules

Support frames and plates, **p. 585 and 594 to 603**

