



2 824 17



2 824 15-C1



2 824 39-C

Conform to IEC 60669 standard  
Material: Polycarbonate front cover plates  
Dimensions: 86 x 88 mm  
Supplied with 2 screws M 3.5 for BS boxes. Supplied complete with plate

Pack	Cat.Nos	Hotel guest room indicators
1	2 824 17	<p>Enable the guest to inform hotel staff of the room status Two settings are possible: - do not disturb (DND) - please clean-up the room (CUR)</p> <p><b>Indicator lamp and bell button</b> Installed in the corridor Double function: call indicator and bell button 1-gang, black touch plate</p> <p><b>DND/CUR control units for guest room</b> Installed in the guest room Allow the user to select the desired setting</p> <p>○ White (Silver bar) ● Matt Black (Electroplate bar) ● Rose Gold (Electroplate bar) ● Champagne (Silver bar) ● Dark Silver (Silver bar)</p>
8	2 824 16	<p><b>Keycard switches - 230 V~ - 16 A</b></p> <p>Supplied with one card</p> <p>○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver</p>
8	2 824 16-C	
8	2 824 16-C1	
8	2 824 16-C2	
8	2 824 16-C3	
5	2 824 18	<p><b>RFID keycard switches - 230 V~ - 16 A</b></p> <p>Compatible with ISO type contactless keycards</p> <p>○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver</p>
5	2 824 18-C	
5	2 824 18-C1	
5	2 824 18-C2	
5	2 824 18-C3	
1	2 824 39	<p><b>Shaver sockets</b></p> <p>Conform to IEC 61558-2-8 115/230 V - 20 VA - 50/60 Hz Power supply: 230 V~ - 50/60 Hz Suitable for use with European, British, Australian, Chinese and US 2-pin plugs Dim: 86 x 146 mm 2 outputs</p> <p>○ White ● Matt Black ● Rose Gold ● Champagne ● Dark Silver</p>
1	2 824 39-C	
1	2 824 39-C1	
1	2 824 39-C2	
1	2 824 39-C3	



2 824 70-C1



2 824 71-C2

Pack	Cat.Nos
15	2 824 70
15	2 824 70-C
15	2 824 70-C1
15	2 824 70-C2
15	2 824 70-C3

**Blanking plates**




- White
- Matt Black
- Rose Gold
- Champagne
- Dark Silver

20	2 824 72
20	2 824 72-C
20	2 824 72-C1
20	2 824 72-C2
20	2 824 72-C3
5	2 824 73
5	2 824 73-C
5	2 824 73-C1
5	2 824 73-C2
5	2 824 73-C3
5	2 824 74
5	2 824 74-C
5	2 824 74-C1
5	2 824 74-C2
5	2 824 74-C3
5	2 824 75
5	2 824 75-C
5	2 824 75-C1
5	2 824 75-C2
5	2 824 75-C3


**Frames for multi-gang installation**

**2-gang frame**




- White
- Matt Black
- Rose Gold
- Champagne
- Dark Silver

**3-gang frame**




- White
- Matt Black
- Rose Gold
- Champagne
- Dark Silver

**4-gang frame**



- White
- Matt Black
- Rose Gold
- Champagne
- Dark Silver

**5-gang frame**



- White
- Matt Black
- Rose Gold
- Champagne
- Dark Silver

15	2 824 71
15	2 824 71-C
15	2 824 71-C1
15	2 824 71-C2
15	2 824 71-C3

**Arteur adaptors**

For 2-module products



- White
- Matt Black
- Rose Gold
- Champagne
- Dark Silver